

Feature

- Memo board can be folded away to put in.
- Nesting function is supplied so they can be stacked when being put in.



Nesting Example (green)



Black

CHAIR WITH MEMO BOARD

Order No.	Model No.	Color	Seat×Height (mm)	JPY	Ref.No
3-5168-01	SNC-ST6MABK	Black	435×460×445	¥ 19,000	075860
3-5168-02	SNC-ST6MAG	Green		¥ 19,000	075860

Specification

- Material: Upholstery/fabric, Seat/plywood, Backrest/PP (polypropylene), Frame/steel, Cushion material/urethane foam, Caster/PA (nylon)
- Dimensions: Outer dimensions/620×560×740mm, Backrest/485×205mm, Memo board/365×280mm
- Seat withstand load: 80kg
- Weight: approx.7kg

Reseachers' Desks·Chairs



Blue

Brown

FOLDING CHAIR

Order No.	Model No.	Color	JPY	Ref.No
3-5169-01	SFC-2T·BL	Blue	¥ 3,600	075860
3-5169-02	SFC-2T·BR	Brown	¥ 3,600	075860

Feature

- Cylinder mode is adopted to prevent fingers from getting pinched.

Specification

- Material: Upholstery/Synthetic Leather (leather-like PU (polyurethane)), Frame/Steel Pipe (φ22.2mm) Powder Coating (silver)
- Dimensions: 450×470×765 (440)mm

PARTITIONINGS FOR WORKING



Order No.	Model No.	Type	Dimensions (mm)	Weight	JPY	Ref.No
1-7271-01	SF-30A35	Single Unit	900×30×1500	8	¥ 29,480	075860
1-7271-02	SF-30A45		1200×30×1500	9.5	¥ 40,810	075860
1-7271-03	SF-30A35C	Coupling Unit	900×30×1500	6.3	¥ 24,310	075860
1-7271-04	SF-30A45C		1200×30×1500	7.8	¥ 35,640	075860
1-7271-11	SF-30A-15I	(For Height 1500) Pole For Corner	30×30×1500	1.7	¥ 3,850	075860
1-7272-01	SF-30A36	Single Unit	900×30×1800	8.7	¥ 32,890	075860
1-7272-02	SF-30A46		1200×30×1800	10.1	¥ 43,890	075860
1-7272-03	SF-30A36C	Coupling Unit	900×30×1800	7.1	¥ 26,730	075860
1-7272-04	SF-30A46C		1200×30×1800	8.4	¥ 37,730	075860
1-7272-11	SF-30A-18I	(For Height 1800) Pole For Corner	30×30×1800	2.0	¥ 4,840	075860
1-7271-12	30-CS	Caster Set	-	-	¥ 2,000	075860

※ Pole (with safety board) is included 2pieces in Single unit, and 1piece in Coupling Unit.

Specification

- Material: Panel/Aluminum Rib Plate, Support/Aluminum, Upper Transparent Window/Recycled PVC (polyvinyl chloride)
- Caster: φ40mmNylon
- Caster Set (30-CS) Accessories: Caster with Stopper·Caster withoutStopper×each 1piece



SF-30A45

SF-30A35C



30-CS Use Example

Feature

- Only screwdriver is required to assemble and disassemble.

PERTITION (Magnet Connection Type)

Order No.	Model No.	Specification	Dimensions (mm)	JPY	Ref.No
3-5233-01	SMP-1506MP·NA	Body·Natural	600×20×1525	¥ 13,800	075860
3-5233-02	SMP-1506PC	Body·Clear Frost	1525	¥ 13,800	075860
3-5233-03	SMP-1806MP·NA	Body·Natural	600×20×1825	¥ 15,800	075860
3-5233-04	SMP-1806PC	Body·Clear Frost	1825	¥ 15,800	075860
3-5233-05	SMP-1509MP·NA	Body·Natural	900×20×1525	¥ 17,800	075860
3-5233-06	SMP-1509PC	Body·Clear Frost	1525	¥ 17,800	075860
3-5233-07	SMP-1809MP·NA	Body·Natural	900×20×1825	¥ 19,800	075860
3-5233-08	SMP-1809PC	Body·Clear Frost	1825	¥ 19,800	075860
3-5233-11	SMP-SJ	Straight Connecting Brackets	1set (upper/lower of each)	¥ 1,500	075860
3-5233-12	SMP-LJ	L-type Connecting Brackets		¥ 1,500	075860
3-5233-13	SMP-3J	3-ways Connecting Brackets		¥ 2,100	075860
3-5233-14	SMP-4J	4-ways Connecting Brackets	1piece	¥ 2,700	075860
3-5233-15	SMP-F	Stabilizing Feet with Adjuster	1piece	¥ 1,800	075860
3-5233-16	SMP-FK	Caster Stabilizing Feet		¥ 1,900	075860

※ Stabilizing feets are not supplied with body.

※ When stabilizers with caster are used, connecting brackets cannot be used.

Feature

- They are connected with magnetic force, therefore you can make them connected not only with another panel but also with steel book shelf or locker.



Natural

Clear Frost



Straight Connection

4-ways Connection

Adjuster Feet

Caster Feet

Specification

- Material: Frame/Steel (powder coating), Panel/MDF (4mm thickness) Vinyl Chloride Sheet Upholstery (natural), Clear Frost/PC (polycarbonate)

1 Laboratory Equipment

2 Measuring Equipment

3 Laboratory Furniture

4 Life Science and Analysis

5 Bottles and Containers

6 Laboratory Related Tools and Fixtures

7 Cleaning and Sterilization

8 Safety Protection Supplies

9 Clean Environment Equipment

A Laboratory Tables

B Cabinets

C Fume Hoods/Clean Bench/Glove Boxes

D Desiccators

E Storage

F Wagons and Ladders