

## Storage Cases



A4-M18P



A4-36P



B4-M20P



B4-18P

### FLOOR CASES

Order No.	Model No.	Dimensions (mm)	Drawers	JPY	Ref.No
3- 286-03	A4-M18P	537×341×880	18 (2lines・9tiers)	¥ 52,500	092650
3- 286-05	A4-M27P	796×341×880	27 (3lines・9tiers)	¥ 81,500	092650
3- 286-02	A4-18P	278×341×880	18 (1lines・18tiers)	¥ 38,000	092650
3- 286-04	A4-36P	537×341×880	36 (2lines・18tiers)	¥ 65,000	092650
3- 286-06	A4-54P	796×341×880	54 (3lines・18Columns)	¥ 95,000	092650

### FLOOR CASE

Order No.	Model No.	Dimensions (mm)	Drawers Capacity	JPY	Ref.No
3- 291-09	B4-M10P	312×411×880	10 (1line・10tiers)	¥ 40,000	092650
3- 291-11	B4-M20P	596×411×880	20 (2lines・10tiers)	¥ 65,000	092650
3- 291-14	B4-M30P	880×411×880	30 (3lines・10tiers)	¥ 98,000	092650
3- 291-10	B4-18P	312×411×880	18 (1line・18tiers)	¥ 46,500	092650
3- 291-13	B4-54P	880×411×880	54 (3lines・18tiers)	¥ 115,000	092650

### DIVIDERS

Order No.	Model No.	Suitable Drawer	Type	JPY	Ref.No
3- 280-11	AS-105	For Shallow Drawer (5pieces)	Side	¥ 1,300	092650
3- 280-12	AS-205	For Shallow Drawer (5pieces)	Vertical	¥ 1,600	092650
3- 280-13	AM-105	For Deep Drawer (5pieces)	Side	¥ 2,000	092650
3- 280-14	AM-205	For Deep Drawer (5pieces)	Vertical	¥ 2,600	092650

#### ■ Specification

- Material : Body/Steel, Drawer/Transparent Styrene Resin
- Drawer Inner Dimensions : A4-M18P・A4-M27P/225×311×75mm, A4-18P・A4-36P・A4-54P/225×311×32mm

### DIVIDERS

Order No.	Model No.	Suitable Drawer	Type	JPY	Ref.No
3- 291-21	B5-105	For B4 Shallow Drawer (5pieces)	Side	¥ 2,000	092650
3- 291-22	B5-205	For B4 Shallow Drawer (5pieces)	Vertical	¥ 2,600	092650
3- 291-23	BM-105	For B4 Deep Drawer (5pieces)	Side	¥ 2,600	092650
3- 291-24	BM-205	For B4 Deep Drawer (5pieces)	Vertical	¥ 3,050	092650

#### ■ Specification

- Material : Body/Steel, Drawer/Transparent Styrene Resin
- Drawer Inner Dimensions : B4-M10P・B4-M20P・B4-M30P/259×382×74mm, B4-18P・B4-54P/259×382×37mm



AF-SM9



AF-SH12



AF-S18



AF-ST2

### SECURITY FLOOR CABINETS (A4・Vertical Type) JP

Order No.	Model No.	Dimensions (mm)	No. of Drawers	Weight (kg)	JPY	Ref.No
1-3439-01	AF-SM9-White	277×366×880	Deep 9	10.2	¥ 37,500	092640
1-3439-02	AF-SH12-White		Shallow 6・Deep 6	10.5	¥ 37,500	092640
1-3439-03	AF-S18-White		Shallow 18	11.8	¥ 37,500	092640
1-3439-04	AF-ST2-White		Shelf Board 3	8.7	¥ 37,500	092640

#### ■ Specification

- Material : Body・Rack Board (AF-ST2)/Steel Powder Baked Finish, Drawer/PS (polystyrene)
- Drawer Inner dimensions : Deep/233×307×80mm, Shallow/233×307×36mm
- Rack Board Pitch : 30mm (AF-ST2) ● Key provided
- Accessories : Title Card (AF-SM9・SH12・S18), Rack Board×2 (AF-ST)

### PICK LL CABINET JP

Order No.	Model No.	Dimensions (mm)	JPY	Ref.No
3- 281-04	LL-30H	570×255×880	¥ 58,000	092650
3- 281-05	LL-32H		¥ 58,000	092650

### DRAWER DIVIDERS JP

Order No.	Model No.	Suitable Drawer	Type	JPY	Ref.No
3- 281-01	DP-1	For Large Type	Side Type	¥ 330	092650
3- 281-02	DP-2	For Middle Type		¥ 300	092650
3- 281-03	DP-3	For Small Type		¥ 250	092650

#### ■ Specification

- Material : Body/Steel, Drawer/Transparent Styrene Resin
- Drawer Inner Dimensions : Large/250×221×75mm, Middle/119×221×75mm, Small/75×221×75mm
- Drawer Composition : LL-30H/Large・Middle・Small, LL-32H/Middle
- Divider Provided : LL-30H/30, LL-32H/32



LL-30H



LL-32H

1 Laboratory Equipment

2 Measuring Equipment

3 Laboratory Furniture

4 Life Science and Analysis

5 Bottles and Containers

6 Laboratory Related Tools and Fixtures

7 Cleaning and Sterilization

8 Safety Protection Supplies

9 Clean Environment Equipment

A Laboratory Tables

B Cabinets

C Fume Hoods/ Clean Bench/ Glove Boxes

D Desiccators

E Storage

F Wagons and Ladders