

1 Laboratory Equipment

2 Measuring Equipment

3 Laboratory Furniture

4 Life Science and Analysis

5 Bottles and Containers

6 Laboratory Related Tools and Fixtures

7 Cleaning and Sterilization

8 Safety Protection Supplies

9 Clean Environment Equipment

A Glass Supplies

B Measuring Apparatuses

C Test Tubes and Funnels

D Plugs and Pipettors

E General Laboratory Supplies

F Tubings and Connectors

G Materials

H Chemicals

I Field Supplies for Industrial Use

J Tape, Paper Products

K Timers, Electrical Equipment and Tools

L Stationary and Others

Parafilm® Wraps

MEMBRANE SEAL (MilliSeal™)

Ask Us

Order No.	Model No.	Filter Dia.* (mm)	JPY	Ref.No
5-5644-01	FWMS01800	18	Ask Us	171785

※ Including peripheral edge viscosity ring parts of 4mm width.

■ Specification

- Hole Dia. : 0.45mm
- Thickness : 0.2mm
- Material : PTFE (fluororesin), Adhesive Antitoxic Acrylics Base
- Sterilization Operation (autoclave・γ Rays sterilization・EDG) is impossible.
- Quantity : 1box (375sheets)

■ Feature

- PTFE sealing material sealing with breathability.
- Prevent contamination from air floating fines, such as dew condensation, mold, spore and dust.



STRETCH FILM

Order No.	Model No.	Width×Length×Thickness	Quantity	JPY	Ref.No
2-9928-03	NES	500mm×450m×8μm	1bag(8rolls)	¥7,200	171775
2-9928-01	FK	500mm×300m×15μm	1bag	¥5,250	171775
2-9928-02	FB	500mm×300m×17μm	1bag(6rolls)	¥5,750	171775

■ Specification

- Material : PE (polyethylene) ● Paper Tube : NES / 2 inch, FK / 3 inch
- Tensile Fracture Strength (JIS Z-1702 compliant) : NES / Vertical 50MPa or more · Lateral 20MPa or more, FK / Vertical 35MPa or more · Lateral 25MPa or more, FB / Vertical 40MPa or more · Lateral 25MPa or more
- Accessories : Dedicated Adapter × 2 (NES only)

■ Feature

- Features outstanding elasticity and transparency.



■ Quantity of Case

- 20m Roll / 60pieces, 50m Roll / 30pieces

WRAPS

JP

Order No.	Model No.	Width×Length	JPY	Ref.No
1-7442-01	Regular YB-3020	300mm×20m	¥200	171760
1-7442-02	High Wrap® PO100	300mm×100m	¥980	171760

■ Feature

- Chlorine system not generated which causes dioxin even if combusted.
- Disposal of blade is as combustible waste (natural material, YB-3020).

■ Specification

- Material : polyethylene ● Heat Resistant Temperature : 110℃

WRAPS

JP

Order No.	Width×Length	JPY	Ref.No
1-8063-03	150mm×20m	¥230	171770
1-8063-02	220mm×20m	¥280	171770
6-718-01	300mm×20m	¥300	171770
1-8063-01	300mm×50m	¥830	171770

※ The price is per piece.

■ Specification

- Material : PVDC (polyvinylidene chloride)



WRAPS

JP

Order No.	Model No.	Width×Length	JPY	Ref.No
1-3785-01	22×50	220mm×50m	¥470	171710
1-3785-02	30×50	300mm×50m	¥520	171710
1-3785-03	30×100	300mm×100m	¥980	171710

■ Feature

- Highly stretchy, excellent in strength and viscosity.
- Slim and easy to use, crushable and disposal is easy as well.

■ Specification

- Material : PVC (polyvinyl chloride)
- Heat Resistant Temperature : 130℃ ● Rewinding Protection Equipped

STRETCH FILM(Coreless wrap)

Order No.	Width×Thickness×Length	Quantity	JPY	Ref.No
1-7303-01	500mm×17μm×300m	6rolls	¥10,600	171760

■ Feature

- It is stretch film which enhances efficiency of distribution.
- Lightweight as liner paper (recycled paper) is adopted as winding core.
- Winding core is not industrial waste, fuss-free to process different from conventional paper tube.

■ Specification

- Adhesive Strength : 44mN/100mm ● Tear Strength : Vertical Direction / 475N/1m, Horizontal Direction / 2185N/1m (JIS-P8116)
- Material : Film / L-LDPE (3layers), Core / Liner Paper (recycled paper)
- Weight : 2.4kg