

AXEL

NETSUKEN

2-615-11 Platinum Digital Thermometer Standard Sensor SN-3400-01



Order No. 2-615-11
Model No. SN-3400-01
JAN Code 4582394450778

Standard price
JPY: 6,000
USD: 40.10

Exchange rate 1USD= 149.64JPY
Valid price in Japan

Quantity 1piece



Calibration Available

Features

- This is highly accurate platinum thermometer.

Spec

- Body indicated temperature range: -100 to +400°C
- Resolution: 0.1°C
- Body measurement accuracy: -50 to +200°C/±0.3°C, Other/±0.8°C
- Input sensor: Platinum resistance thermometer Pt1000, class A
- Waterproof function: IPX5
- Function: Clock, memory (99 memories), HOLD, MAX/MIN, key lock, auto power OFF, external data output
- Material: ABS resin (antibacterial)
- Power supply: AA battery x 2 pieces (included for testing)
- Weight: 160g
- With strap
- Standard sensor (-100 to +300°C)
- Size (mm): φ3 x 100
- Platinum thermo
- *Sensor probe is not included in the package.
- Model number: SN-3400-01

▶ Package size : 295×90×20 mm 90 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	548
AS ONE Catalog 2021 [Instruments for Laboratory]	504
AS ONE Catalog 2019 [Instruments for Laboratory]	481
AS ONE Catalog 2017 [Instruments for Laboratory]	384
AS ONE Catalog 2015 [Instruments for Laboratory]	349