

# AXEL

## 2-8180-01 Clamp Meter AC/DC M290RMS



Order No. 2-8180-01

Model No. M290RMS

**JPY:**  
**34,000**

Standard price

**USD:**  
**227.21**

Exchange rate 1USD= 149.64JPY

Valid price in Japan

Quantity 1 unit



Calibration Available

### Features

- This compact meter achieves effective value (RMS) which offers wide measurement range of up to AC/DC 400A.
- Suitable for current control in electrical paths with distorted waveforms such as inverter.
- In DC current measurement, point can be adjusted easily with a single push.

### Spec

- Model number: M290RMS
- Measurement range: AC/DC current/0 - 400.0A, AC/DC voltage/0 - 600.0V, Resistance/0 - 999.9Ω
- Accuracy: AC/DC current, resistance/  $\pm 1.5\%rdg$ , AC/DC voltage/  $\pm 1.0\%rdg$
- Display: 4000 counts
- Power supply: AAA alkaline battery x 3 pieces (included for test)
- With auto power OFF function
- Accessories: Soft case
- Size: 44 x 24 x 180mm
- Weight: 135g

▶ Package size : 80×185×40 mm 140 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	801
AS ONE Catalog 2021 [Instruments for Laboratory]	744
AS ONE Catalog 2019 [Instruments for Laboratory]	721
AS ONE Catalog 2017 [Instruments for Laboratory]	558