

AXEL

3M Company

2-9691-01 Soldering Plug 10114-3000 PE 10114-3000PE



Order No.	2-9691-01
Model No.	10114-3000PE
JAN Code	0000000000000
	JPY: 850
	USD: 5.68
Standard price	
	Exchange rate 1USD= 149.64JPY
	Valid price in Japan
Quantity	1piece

Spec

- Material: Body/glass reinforced polyester, Shroud/copper, Contact/copper alloy
- Applicable product: Cable/AWGNo.24 - 30, Shell system/MDR non shield shell kit (straight type): 2-9692-01 - 05, 2-9693-01 - 04
- Rating voltage: AC/maximum 150V, DC/maximum 200V
- Rated current: Maximum 0.5A
- Ambient temperature: -55 - 85°C
- Number of poles: 14
- Color: Black
- Miniature delta ribbon
- MDR system
- Model number: 10114-3000PE

▶ Package size : 50×50×50 mm 100 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2015 [Instruments for Laboratory]	1630