

AXEL

3-6700-01 Digital Storage Oscilloscope 50MHz DSO3050E



Order No. 3-6700-01
Model No. DSO3050E
JAN Code 4582110954184

Standard price
JPY:
48,500
USD:
326.27

Exchange rate 1USD= 148.65JPY
Valid price in Japan

Quantity 1piece



Features

- Able to carry out 20 different types of automatic measuring and FFT analysis.
- With depth of 78*mm* and weighing just 1.5*kg*, this device is extremely compact.
- 8-inch LCD display panel allows easy menu navigation.
- Equipped with pass/fail, waveform recording, and replay functions.

Spec

- Model number: DSO3050E
- Frequency band (MHz): 50
- Sample rate (GS/s): 0.5
- Analog, number of channels: 2
- Record length: 10k points
- Rise time: $7 \leq ns$
- Vertical axis resolution: 8 bits
- Vertical axis input sensitivity range: 5mV/div - 5V/div
- DC gain accuracy: +/- 3%
- Input impedance: $1M\Omega \pm 2\%$, $10pF \pm 5pF$
- Waveform calculation: + · - · x · ÷
- Arithmetic functions: FFT
- Cursor measurement: ΔV , ΔT
- Automatic measurement: P-P, Average value, RMS, Frequency, Cycle, Maximum value, Minimum values, Rise time, Fall time, Delay, + Width, - Width, Duty, etc.
- Trigger type: Edge, Pulse width, Video, Slope, etc.
- Trigger mode: Auto, Normal, Single
- Interface: USB, LAN
- Size: 348 x 78 x 170mm
- Weight: 1.5kg
- Power supply: 100VAC 50/60Hz
- *Sample rate is the value of the single channel.

» Package size : 120×420×220 mm 2.3 kg