

AXEL

KANOMAX JAPAN INCORPORATED

1-6515-11 Anemomaster Wind Velocity Meter MODEL6006



Order No.	1-6515-11
Model No.	MODEL6006
JAN Code	4562288760060
	JPY: 59,800
	USD: 399.63
Standard price	
	Exchange rate 1USD= 149.64JPY
	Valid price in Japan
Quantity	1unit

Features

- Compact anemometer which can operate all with one button.
- Temperature compensation circuit built-in.

Spec

- Model number: MODEL6006
- Measurement range (wind speed/wind temperature): 0.1 - 20.0m/s/-20 - 70°C
- Resolution: Wind speed/0.01m/s (0 - 9.99m/s), 0.1m/s (10.0 - 20.0m/s), Wind temperature/0.1°C
- Accuracy: Wind speed/+/- 5% or 0.015m/s of indicated value, whichever is larger, Wind temperature/+/- 1°C
- Temperature compensation accuracy: +/- 5% or 0.015m/s of indicated value, whichever is larger (in the range of 10 - 40°C)
- Probe usable temperature range: -20 - 70°C (body/5 - 40°C)
- Power supply: AA battery x 4 (included for testing)
- Size: Body/60 x 34 x 120mm, Probe/φ6.1 (φ10.6) x 205mm (cable/1.5m)
- Weight: Approximately 180g (including cell)
- Accessories: Extension bar (elastic type 166 - 909mm) x 1, Carrying case x 1

▶ Package size : 280×230×70 mm 1.04 kg

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	771
ASONE Catalog 2022 [Facility & Equipment for Laboratory]	379
AS ONE Catalog 2021 [Instruments for Laboratory]	712
AS ONE Catalog 2019 [Instruments for Laboratory]	691
AS ONE Catalog 2017 [Instruments for Laboratory]	540
AS ONE Catalog 2015 [Instruments for Laboratory]	509
ASONE Catalog 2020 [Facility & Equipment for Laboratory]	338
ASONE Catalog 2018 [Facility & Equipment for Laboratory]	351
ASSRE Catalog 2016 [Facility & Equipment for Laboratory]	319