

AXEL

KANOMAX JAPAN INCORPORATED

1-6516-11 Climomaster Wind Velocity Meter 6501-00



Order No.	1-6516-11
Model No.	6501-00
JAN Code	0000000000000
	JPY: 128,000
	USD: 855.39
Standard price	
	Exchange rate 1USD= 149.64JPY
	Valid price in Japan
Quantity	1unit

Calibration Available

Features

- Measuring accuracy is the top class of thermal anemometer.
- It corresponds to measured temperature range of minus (- 20~70°C) .
- Air flow switching is easy to register duct dimensions in advance.
- 6531-21 · 6541-21 : Suitable for the place where wind direction is known such as air inlet and outlet of air-conditioning equipment.
- 6542-21 : Horizontal omnidirection. No concerning to wind direction at inserting into the duct. Good for small inspection hole.
- 6551-21 : Suitable for measuring at narrow spaces with omnidirectional *01* miniature spherical sensor and shield cable.
- 6533-21 · 6543-21 : Horizontal omnidirection. Wide vertical omnidirection. Suitable for room where wind direction is not known (such as clean room) .

Spec

- Model number: 6501-00
- Body
- Accuracy: Wind speed/± 2%rdg or 0.015m/s, whichever is larger
- Output function: Digital output, USB (auto-switching to RS-232C at the time of connecting to printer)
- Size: 88 x 51 x 188mm
- Weight: 260g
- Power supply: AA battery x 6 (rechargeable battery "Ni - Cd, Ni-MH" available), AC adapter (AC100 - 240 50/60Hz)
- Accessories: AA manganese battery x 6, Probe cable (2m) x 1, USB cable x 1, Carrying case x 1
- *Probe is sold separately.

▶ Package size : 360×430×100 mm 2.27 kg

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	772