

AXEL

ENGINEER. INC.

2-185-02 Light Loupe with Cover SL-40



Order No.	2-185-02
Model No.	SL-40
JAN Code	4989833058401
Standard price	JPY: 33,000
	USD: 222.00
Quantity	1 unit

Exchange rate 1USD= 148.65JPY
Valid price in Japan



Features

- The magnifier can be installed vertically and horizontally.
- There is no flickering of light by inverter circuit and there is no fatigue eyes even after long-time work.
- It can move by one action enlarge the subject sharply, and brightly and freely.

Spec

- Power supply: AC100V 50/60Hz
- Overall height: 950mm
- Fluorescent lamps: 28W
- Cord length: 1.9m
- Weight: 2.2kg
- Maximum plate thickness for clamp: 55mm
- Clamp adjustable angle: 15 - 50°
- Loupe movable range: Horizontal/- 1150mm, Vertical direction/- 950mm
- Accessories: Round fluorescent lamps, clean paper cover to protect a lens
- Model number: SL-40
- Magnification: 2.0 x
- Lens diameter (φmm): 140
- RoHS3 (EU)2015/863 Certificates can be issued

▶ Package size : 340×600×170 mm 3.57 kg

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	966
AS ONE Catalog 2021 [Instruments for Laboratory]	879
AS ONE Catalog 2019 [Instruments for Laboratory]	857
AS ONE Catalog 2017 [Instruments for Laboratory]	673