

# AXEL

## 2-1960-01 Digital Thermo-Hygrometer (Built-In Data Logger) MT-309



Order No.	2-1960-01
Model No.	MT-309
JAN Code	4986702302245
	<b>JPY:</b> <b>38,000</b>
	<b>USD:</b> <b>255.63</b>
Standard price	
	Exchange rate 1USD= 148.65JPY
	Valid price in Japan
Quantity	1unit

Calibration Available

### Features

- 4-channel measurement and display at the time is possible.
- Saves up to 16000pieces of data.

### Spec

- Model number: MT-309
- Body
- Measurement range: -200 to +1370°C
- Body accuracy: -200 to +200°C , 400 - 1370°C/±(0.3%rdg + 1°C), 200 - 400°C/±(0.5%rdg + 1°C)
- Resolution: 0.1°C (0 - 200°C), 1°C (other than the left)
- Sensor: K class thermocouple
- Sampling: 3 times/second
- Display unit: Switching between Celsius and Fahrenheit
- Function: Data logger (maximum 16000 data), data hold, temperature deviation, maximum/minimum value display, auto power off, battery exhaustion display
- Interface: USB
- Power supply: 006P (9V) dry cell x 1 (test included) or AC adapter (optional)
- Size: 64 x 30 x 184mm
- Weight: Approx 320g
- Accessories: Beads type K thermocouple sensor TPK-01 x 2, RS-232C cable, software, Carrying case

» Package size : 170×315×80 mm 830 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	645
AS ONE Catalog 2021 [Instruments for Laboratory]	604