

# AXEL

AS ONE Corporation

## 1-4598-11-20 Digital OverTemperature Control Device With Calibration Certificate OP-1000A



Order No.	1-4598-11-20
Model No.	OP-1000A
JAN Code	4589638258145
Standard price	<b>JPY:</b> <b>57,500</b>
	<b>USD:</b> <b>382.39</b>
	Exchange rate 1USD= 150.37JPY Valid price in Japan
Quantity	1piece



### Features

- When the temperature rises above the set temperature, the power is automatically turned off (reset means turning the power back on).
- A jog dial system enables quick and reliable temperature settings.
- The display screen is a backlit liquid crystal screen with excellent visibility that simultaneously displays the set temperature and the measured temperature.

### Spec

- Model number: OP -1000 A
- Setting range (°C): 20.0 to 500.0
- Minimum Display Unit (°C): 0.1
- Temperature display accuracy:  $\pm 2.6$  °C
- Sensor: K class thermocouple
- Connected capacity: AC100V MAX 12 A
- Safety Device: Sensor Error Detection Circuit Protector
- Temperature setting method: LCD digital display (simultaneous display of the set and measured temperatures)
- Additional functions: Setting value memory key lock
- Power supply : AC100V 50/60Hz
- Size: 147 x 150 x 106mm
- Accessories: K class thermocouple x 1 piece
- \*Even if the temperature drops after power supply is cut due to overheating, it won't recover.
- Accessories: Calibration certificates
- \*Products with calibration certificate is a service where equipment is calibrated and calibration certificate is issued at the time of shipment.

› Package size : 270×370×190 mm 1.61 kg

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	567