

AXEL

1-1942-01-20 Data Logger Conductivity Meter With Calibration Certificate CD-4307SD



Order No.	1-1942-01-20
Model No.	CD-4307SD
JAN Code	4589638257858
	JPY: 54,800
	USD: 364.43
Standard price	
	Exchange rate 1USD= 150.37JPY Valid price in Japan
Quantity	1piece



Features

- Calibration certificate attached includes the calibration certificate, inspection report and traceability chart of Conductivity at the time of shipment.
- Calibration Certificate attached is AsOne original certificate service.
- Data saved on the SD card can be downloaded to the PC and edited in Excel (R).
- TDS (Soluble Substances) and salt concentration can also be measured.

Spec

- Model number: CD -4307 SD
- Size: 68 x 45 x 177mm
- Measurement item: Conductivity, TDS, salinity concentration, and temperature
- Conductivity: 0 to 200.0 μ S/cm, 0.2 to 2.0mS/cm, 2 to 20.0mS/cm, 20 to 200.0mS/cm
- TDS: 0 to 132.0 ppm, 132 to 1320 ppm, 1320 to 13200 ppm, 13200 to 132000 ppm
- salinity concentration: 0 to 12.0% salt
- Temperature/0 to 60.0 $^{\circ}$ C
- Weight: about 489g
- Display: 3-digit LCD with backlight
- Interface: RS 232 C, USB output
- Power supply : AA size battery x 6 pieces (test attachment) or AC adapter (Sold separately)
- Accessories: Conductivity/TDS/salinity concentration electrode, SD card (1GB), hard carrying case
- Accessories: Calibration certificates
- *Products with calibration certificate is a service where equipment is calibrated and calibration certificate is issued at the time of shipment.

▶ Package size : 265×370×120 mm 1.38 kg

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	674
AS ONE Catalog 2021 [Instruments for Laboratory]	635