

AXEL

AS ONE Corporation

1-3460-02 Sound Level Meter TM-103



Order No.	1-3460-02
Model No.	TM-103
JAN Code	4560111737371
	JPY: 38,800
	USD: 261.02
Standard price	
	Exchange rate 1USD= 148.65JPY
	Valid price in Japan
Quantity	1unit

Features

- EN61672 type 2 compliant.
- TM-103 model is equipped with memory and data output functionality.
- TM-100 model allows user to check noise meter operation and perform calibration.

Spec

- Model number: TM-103
- Measurement range (dB): 30 - 130
- Resolution (dB): 0.1
- Frequency range: 31.5Hz - 8kHz
- Switching range: Low/30 - 80dB, Med/50 - 100dB, Hi/80 - 130dB
- Accuracy (94dB/1kHz when): ± 1.5 dB
- Function: MAX/MIN display, data hold, auto off timer, display section backlight, Memory (14,000 data), Data input (USB interface)
- Power supply: 006P (9V) dry cell x 1 piece (included for test)
- Size/weight: 56 x 32 x 280mm/ 290g
- Accessories: Exclusive software (CD-ROM, Windows(R) 2000/XP/7/8 correspondence)

▶ Package size : 295×205×75 mm

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	776
AS ONE Catalog 2021 [Instruments for Laboratory]	718
AS ONE Catalog 2019 [Instruments for Laboratory]	697
AS ONE Catalog 2017 [Instruments for Laboratory]	545
AS ONE Catalog 2015 [Instruments for Laboratory]	512