

# AXEL

## 1-3558-01 High Precision Digital Pressure Indicator KDM30-500kPaG-M-BL



Order No.	1-3558-01
Model No.	KDM30-500kPaG-M-BL
	<b>JPY:</b> <b>39,500</b>
	<b>USD:</b> <b>265.73</b>
Standard price	
	Exchange rate 1USD= 148.65JPY Valid price in Japan
Quantity	1piece

Calibration Available

### Features

- Equipped with flexible display which allows head and display angle rotate 330°.

### Spec

- Measuring range: 0 ~ 500.0 kPaG
- Power supply: 24 VDC (external power supply)
- Power: 4 ~ 20 mA, Warning HI/GO/LO/NPN
- Measuring fluids: Gases and liquids (fluids that do not corrode SUS 316 L)
- Accuracy: +/- 0.25% FS +/- 1 deg (including linearity, hysteresis and reproducibility)
- Features: Sampling time/Display rate/Rate average count selection/Peak/Valley-hold zero point correction/Auto power off
- Materials: Gas and Wetted Parts/Stainless Steel (SUS 316 L), O-Ring/NBR (Nitrile Rubber), Case/ABS Resin
- Connection screw size: G 1/4
- Size: 80 x 48 x 128.5 mm
- Weight: approx. 180 g (battery included)
- With connection cable (1 m)
- Color: Blue
- \*Waterproof and dustproof covers (sold separately) and Bluetooth ® communication type are also available (communication distance: about 8 meters without obstructions). Please inquire.
- \*There are also high-pressure models with a measurement range of 0 ~ 70 MPaG. Please inquire.

▶ Package size : 195×110×75 mm 290 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	814
AS ONE Catalog 2021 [Instruments for Laboratory]	759