

AXEL

GW INSTEK (TEXIO TECHNOLOGY CORPORATION)

1-3887-01 Stabilized DC Power Supply 18V-3A GPS-1830D



Order No.	1-3887-01
Model No.	GPS-1830D
JAN Code	0000000000000
Standard price	JPY: 33,000
	USD: 222.00
	Exchange rate 1USD= 148.65JPY Valid price in Japan
Quantity	1unit

Calibration Available

Features

- Uses series regulator for low-ripple and low-noise operation.
- External control of output voltage or current at 0~10V is available.
- Operation can be in series or parallel.

Spec

- Model number: GPS-1830D
- Output voltage: 0 - 18V
- Output current: 0 - 3A
- Input voltage: AC100/120/220V±10% · 230V+10% 50/60Hz
- Power consumption: 150VA
- Function: Over output, polarity inversion protection
- Power cord length: 1.8m
- Accessories: Test lead (1.0m)
- Size (mm): 127 x 282 x 145
- Weight: Approx 4kg
- CE mark obtained product

▶ Package size : 180×360×215 mm 5.37 kg

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	788
AS ONE Catalog 2021 [Instruments for Laboratory]	728
AS ONE Catalog 2019 [Instruments for Laboratory]	706
AS ONE Catalog 2017 [Instruments for Laboratory]	561