

AXEL

GW INSTEK (TEXIO TECHNOLOGY CORPORATION)

1-4922-11 Digital Storage Oscilloscope GDS-2072A



Order No.	1-4922-11
Model No.	GDS-2072A
JAN Code	0000000000000
Standard price	JPY: 180,000
	USD: 1,202.89
	Exchange rate 1USD= 149.64JPY Valid price in Japan
Quantity	1unit



Calibration Available

Features

- Allows 36 kinds of automatic measurement.
- Transmits image (BMP, PNG) , waveform value (CSV, LSF) and other data to the USB flash memory.
- Divides the memory up to 2048 segments and records the waveform on the segment for each trigger.
- Marks the event satisfying the set search conditions.
- Concurrently measures logic and analog signals of up to 500MS/s and 2M point/ch when incorporating the optional logic analyzer.

Spec

- Number of channels: 2
- Sampling: 2GS/s (for half channel), 1GS/s (for whole channel)
- Maximum memory length: 2M point (for half channel)
- Power consumption: Approximately 55W 80VA
- Vertical resolution/sensitivity: 8 bits, 1mV - 10V/div, 1 - 2 - 5 steps
- Calculation function: Four arithmetic operations (+, -, x, ÷), FFT (dBVrms, Linear rms), extended arithmetic (differential, Integral, √)
- Power supply: AC 100 - 240V, 50/60Hz
- Size: 380 x 145 x 220mm
- Weight: Approx 4.2kg
- Oscilloscope
- Frequency band (MHz): 70
- 2 channels
- Model number: GDS-2072A

▶ Package size : 340×530×275 mm 6.9 kg