

# AXEL

## 1-5793-01 Digital Salimeter EB-158P



Order No.	1-5793-01
Model No.	EB-158P
JAN Code	4582178050019
	<b>JPY:</b> <b>7,500</b>
	<b>USD:</b> <b>50.12</b>
Standard price	
	Exchange rate 1USD= 149.64JPY
	Valid price in Japan
Quantity	1unit

### Features

- Realizes easy operation by simply turning on power supply and pressing its measuring button.
- Realizes high measuring Accuracy of  $\pm 0.1\%$  within practical range 0.0~2.0%.
- Displays salt concentration in % as well as taste level as low, medium and high graphically.
- Available in moisture-proof EB-158DP model for use in humid place such as kitchen (not waterproof) .

### Spec

- Model number: EB-158P
- Measurement range: 0.0 - 5.0%
- Resolution: 0.1%
- Salinity concentration measuring method: Electric conductivity method
- Measurement accuracy:  $\pm 0.1\%$  (0.0 - 2.0%, in the case of solution temperature being room temperature)
- Operating temperature range: 0 - 80°C
- Display system: 2 digit 7 segment LCD (taste level graphic display)
- With automatic temperature compensation function
- Power supply: CR1616 (DC3V) x 1 piece (Cell for test included)
- Size: 30 x 158 x 14mm
- Weight: Approximately 25g (including cell)

▶ Package size : 60×215×20 mm 50 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	848
NAVIS Catalog 2022 [Supplies for Nursing and Medical]	1879
AS ONE Catalog 2021 [Instruments for Laboratory]	792
AS ONE Catalog 2019 [Instruments for Laboratory]	767
AS ONE Catalog 2017 [Instruments for Laboratory]	604
AS ONE Catalog 2015 [Instruments for Laboratory]	572
NAVIS Catalog 2020 [Supplies for Nursing and Medical]	1755
NAVIS Catalog for Clinic 2020 [Supplies for Nursing and Medical]	1755