

# AXEL

Testo K. K.

## 61-0104-18 Pt100 High Precision Temperature Digital Probe For testo735 06140235



Order No.	61-0104-18
Model No.	06140235
JAN Code	4029547002700
	<b>JPY:</b> <b>80,000</b>
	<b>USD:</b> <b>534.12</b>
Standard price	
	Exchange rate 1USD= 149.78JPY Valid price in Japan
Quantity	1piece

### Features

- This thermometer allows you to connect up to 3 temperature sensors (thermocouple x 2, Pt100 x 1) simultaneously.
- With included dedicated software, possible to manage and analyze approx.10,000 data entries.

### Spec

- Measurement range: Temperature/-40 to +300°C
- Accuracy  $\pm 1$  digit:  $\pm 0.05^\circ\text{C}$

» Package size : 580×50×50 mm 290 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	559
AS ONE Catalog 2021 [Instruments for Laboratory]	515
AS ONE Catalog 2019 [Instruments for Laboratory]	492
AS ONE Catalog 2017 [Instruments for Laboratory]	393
AS ONE Catalog 2015 [Instruments for Laboratory]	6161