

# AXEL

## 1-750-13 Static Pressure Tube



Order No.	1-750-13
JAN Code	0000000000000
Standard price	<b>JPY:</b> <b>3,480</b>
	<b>USD:</b> <b>23.41</b>
Quantity	1piece

Exchange rate 1USD= 148.65JPY  
Valid price in Japan



Calibration Available

### Features

- The wide angle scale with readable degree of indicator rotation angle of 270° is attached.
- Highly efficient diaphragm (inside of accuracy error) with little hysteresis.
- It has cap for connection which polarity change is easy.
- < Simple Pitot Tube >
- For standstill air pressure measurement such as room.
- < Static Pressure Tube >
- For measurement of static pressure less than quantity of wind, wind velocity 1m/s in measurement of wind velocity (dynamic pressure) .

### Spec

- Model number: Static pressure tube PTS-VT6-170
- Tube diameter x length:  $\phi 6 \times 170\text{mm}$
- Hole diameter:  $\phi 10.5\text{mm}$
- Connection port (hose nipple): Outer diameter  $\phi 7\text{mm}$

▶ Package size : 80×215×25 mm 70 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	811
AS ONE Catalog 2021 [Instruments for Laboratory]	755
AS ONE Catalog 2019 [Instruments for Laboratory]	733
AS ONE Catalog 2017 [Instruments for Laboratory]	570
AS ONE Catalog 2015 [Instruments for Laboratory]	542