

AXEL

1-750-14 Static Pressure Tube



Order No.	1-750-14
JAN Code	0000000000000
Standard price	JPY: 3,480
	USD: 23.41
	Exchange rate 1USD= 148.65JPY Valid price in Japan
Quantity	1piece

Calibration Available

Features

- The wide angle scale with readable degree of indicator rotation angle of 270° is attached.
- Highly efficient diaphragm (inside of accuracy error) with little hysteresis.
- It has cap for connection which polarity change is easy.
- <Simple Pitot Tube >
- For standstill air pressure measurement such as room.
- <Static Pressure Tube >
- For measurement of static pressure less than quantity of wind, wind velocity 1m/s in measurement of wind velocity (dynamic pressure) .

Spec

- Model number: Static pressure tube PTS-VT4-100
- Tube diameter x length: $\phi 3 \times 100\text{mm}$
- Hole diameter: $\phi 6.5\text{mm}$
- Connection port (hose nipple): Outer diameter $\phi 5.5\text{mm}$

▶ Package size : 115×45×10 mm 20 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	811
AS ONE Catalog 2021 [Instruments for Laboratory]	755
AS ONE Catalog 2019 [Instruments for Laboratory]	733
AS ONE Catalog 2017 [Instruments for Laboratory]	570
AS ONE Catalog 2015 [Instruments for Laboratory]	542