

AXEL

1-9831-01 Digital Illuminometer LX-1108



Order No.	1-9831-01
Model No.	LX-1108
JAN Code	4986702201807
	JPY: 22,000
	USD: 147.02
Standard price	
	Exchange rate 1USD= 149.64JPY Valid price in Japan
Quantity	1unit

Calibration Available

Features

- This product has light source selecting function (4 types) , and measures up to 400,000lx.

Spec

- Model number: LX-1108
- Measurement range (lx): 0 - 40.00/36.0 - 400.0/360 - 4000/3600 - 40000
- Light source target for measurement: Tungsten lamp, fluorescent lamp, sodium lamp, mercury lamp
- Resolution: 40/0.01, 400/0.1, 4000/1, 40000/10, 400000/100
- Accuracy: $\pm(3\%rdg + 0.5F.S)$, reference value if over 100000Lx
- Display function: At peak, Maximum, minimum value (with hold function)
- Front panel section is drip-proof correspondence
- With data holding function
- Power supply: 006P (9V) dry cell x 1 piece (included for test)
- Size: Body/68 x 30 x 200mm, Sensor unit/82 x 55 x 7mm
- Weight: Approx 220g

» Package size : 105×220×65 mm 420 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2021 [Instruments for Laboratory]	705
AS ONE Catalog 2019 [Instruments for Laboratory]	684
AS ONE Catalog 2017 [Instruments for Laboratory]	536
AS ONE Catalog 2015 [Instruments for Laboratory]	503