

AXEL

1-9832-01 Pocket Multimeter MCD008



Order No.	1-9832-01
Model No.	MCD008
JAN Code	4571206800108
	JPY: 5,680
	USD: 37.96
Standard price	
	Exchange rate 1USD= 149.64JPY
	Valid price in Japan
Quantity	1unit



Calibration Available

Features

- Wind up the tester bar by fingertip operation after use.
- The large LC display is easy to read.
- Automatic power OFF function is provided.

Spec

- Model number: MCD008
- DC voltage: Range/0.1mV - 500V, Accuracy/ $\pm 0.7\%rdg \pm 3dgt$
- AC voltage: Range/1mV - 500V, Accuracy/ $\pm 2.3\%rdg \pm 6dgt$
- Resistance: Range/0 - 320 Ω , 3.2K Ω , 32K Ω , 320K Ω , 32M Ω
- Display: Maximum available display, 3200 counts (with bar graph)
- Diode test: Range/0 - 3.2V, Accuracy/ $\pm 10\%rdg \pm 2dgt$
- Continuity test: Buzzer sound
- Power supply: LR-44 button cell x 2 pieces (included)
- Size: 72 x 22.5 x 114mm
- Weight: 110g

▶ Package size : 115×220×30 mm 110 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	799
AS ONE Catalog 2021 [Instruments for Laboratory]	740
AS ONE Catalog 2019 [Instruments for Laboratory]	716
AS ONE Catalog 2017 [Instruments for Laboratory]	554