

AXEL

1-1450-01 Data Logger Thermometer TM-947SD




Order No. 1-1450-01
 Model No. TM-947SD
 JAN Code 4986702202392

JPY:
33,000

Standard price **USD:**
222.00

Exchange rate 1USD= 148.65JPY
 Valid price in Japan

Quantity 1piece



Calibration Available

Features

- Possible to save to SD card, and edit data in Excel just by importing SD card to computer.
- Simultaneous measuring of 4-channels is also possible.

Spec

- Model number: TM-947SD
- Body
- Resolution: 0.1°C, K thermocouple (1000 - 1300°C)/1°C
- Accuracy: +/- (0.4% + 1°C), K thermocouple (-50 - 999.9°C)/+/- (0.4% + 0.5°C)
- Sensor: pT100Ω, Thermocouple (K, J, T, E, R, S)
- Function: Data hold, Max/Min display
- Output: SD card, RS-232C, USB
- Memory: SD card (1G - 16G correspondence)
- Power supply: AA dry cell x 6 pieces (included for test), DC9V (AC adapter optional)
- Size: 177 x 68 x 45mm
- Weight: Approx 489g
- ■Accessories: K thermocouple sensor x 2 volumes (only TPK-01), SD card (1GB), Carrying case

▶ Package size : 150×270×70 mm 660 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	645
AS ONE Catalog 2021 [Instruments for Laboratory]	604
AS ONE Catalog 2019 [Instruments for Laboratory]	572
AS ONE Catalog 2017 [Instruments for Laboratory]	450