

# AXEL

## 1-1715-01 Scratching Method Hardness Tester 318



Order No.	1-1715-01
Model No.	318
	<b>JPY:</b> <b>129,000</b>
	<b>USD:</b> <b>862.07</b>
Standard price	
	Exchange rate 1USD= 149.64JPY
	Valid price in Japan
Quantity	1unit

### Features

- Measure hardness of coated surface with constant loads.
- 318-S is supplied with guide roller.

### Spec

- Model number: 318
- Measurement range: 0 - 20N
- Material: Body/stainless steel, Tip pin/tungsten
- Tip pin:  $\phi 0.75\text{mm}$  (standard),  $\phi 1.0\text{mm}$  (ISO),  $\phi 0.5\text{mm}$
- Size:  $\phi 16 \times 160\text{mm}$
- Weight: 250g
- ERICHSEN

▸ Package size : 180×220×50 mm 310 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	867
AS ONE Catalog 2021 [Instruments for Laboratory]	808
AS ONE Catalog 2019 [Instruments for Laboratory]	783
AS ONE Catalog 2017 [Instruments for Laboratory]	615
AS ONE Catalog 2015 [Instruments for Laboratory]	583