

AXEL

1-2366-01 Voltage/Current Logger LS200-V



Order No. 1-2366-01

Model No. LS200-V

Standard price
**JPY:
21,800**

**USD:
145.68**

Exchange rate 1USD= 149.64JPY

Valid price in Japan

Quantity 1piece



Calibration Available

Features

- Since it can be connected directly to the PC, transfer and retrieval of data is easy.
- Convenient for carrying around lightweight and compact.

Spec

- Model number: LS200-V
- Measurement target: Voltage
- Measurement range: -10 to +10V
- Resolution: 0.4mV
- Accuracy: $\pm 1\% \text{rdg} + 5 \text{dgt}$
- Number of channels: 1 channel
- Measurement interval: 1 second unit/1 - 59 seconds, 1 minute unit/1 - 240 minutes
- With clock function
- Memory: 30000 points (MAX)
- Interface: USB
- Supported OS: Windows(R) 2000/XP (SP2 or later)/VistaTM (32bit)/7 (32bit)
- Power supply: CR1220 button cell (included for test) or CR1225 button cell (optional)
- Size: Body/95.0 x 10.4 x 21.0mm, Probe cable length/100mm
- Weight: Approximately 21g (excluding cell, probe)
- Accessories: Probe for measurement (with red and black clips), body storage bag

▶ Package size : 165×55×25 mm 60 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	801
AS ONE Catalog 2021 [Instruments for Laboratory]	744