

# AXEL

## 1-2517-01 Digital Data Logger MHT-381SD (Thermo-Hygrometer) MHT-381SD



Order No.	1-2517-01
Model No.	MHT-381SD
JAN Code	4986702202521
	<b>JPY:</b> <b>26,800</b>
	<b>USD:</b> <b>179.10</b>
Standard price	
	Exchange rate 1USD= 149.64JPY Valid price in Japan
Quantity	1unit

Calibration Available

### Features

- Data in SD card can be saved PC and edited Excel data.
- Easy-to-read large LCD displays measurement items at the time.

### Spec

- Model number: MHT-381SD (thermo-hygrometer)
- Item to be measured: Temperature, humidity
- Measurement range: (Temperature) 0 - 50°C/(humidity, humidity) 10 - 90%RH
- Resolution: (Temperature) 0.1°C/(humidity, humidity) 0.1%RH
- Accuracy: (Temperature)  $\pm(0.8^{\circ}\text{C})$ /(humidity, humidity)  $\pm 4\%$  rdg + 1%RH (70%RH or higher),  $\pm 4\%$  rdg + 4%RH (lower than 70%RH)
- Sampling: 5/10/30/60/120/300/600 seconds, auto
- Display: 3 digits LCD
- Function: Clocks
- Memory: SD card (1 - 16G)
- Interface: SD card, USB
- Supported OS: Windows(R)2000/XP/VistaTM
- Power supply: AAA dry cell x 6 pieces (included for test) or DC9V (adapter optional)
- Size: 80 x 32 x 132mm
- Weight: Approx 282g
- Accessories: SD card (1G), wall-mounting unit
- CE acquired

▶ Package size : 225×105×65 mm 350 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	638
AS ONE Catalog 2021 [Instruments for Laboratory]	598
AS ONE Catalog 2019 [Instruments for Laboratory]	566