

AXEL

2-9505-21 Portable Tesla Meter MT-801



Order No.	2-9505-21
Model No.	MT-801
JAN Code	4986702101510
	JPY: 100,000
	USD: 667.65
Standard price	
	Exchange rate 1USD= 149.78JPY
	Valid price in Japan
Quantity	1set

Calibration Available

Features

- Covers wide measuring range (0~3000mT (0~30000G)) .
- Provides highly accurate measurement through high resolution measuring method (resolution 0.01mT=0.1G) .
- Transfers data to PC.
- Available with axial sensor (sold separately) for vertical direction measuring

Spec

- Detection target: DC magnetic flux density/polarity (N/S), AC magnetic flux density/40 - 500Hz
- Measurement range: 0 - 3000mT
- Measurement unit: for mT
- Function: Zero reset, Polarity detect, Maximum detected value hold, Auto power OFF
- Power supply: AA battery x 4 (included for test)
- Size of sensor head: 3.5 x 1.0 x 65mm
- Main unit size: 64 x 30 x 140mm
- Weight: 250g
- Accessories: Sensor (MT-801PRB), Carrying case
- Model number: MT-801

▶ Package size : 180×120×50 mm 420 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	889
AS ONE Catalog 2021 [Instruments for Laboratory]	818
AS ONE Catalog 2019 [Instruments for Laboratory]	795
AS ONE Catalog 2017 [Instruments for Laboratory]	625
AS ONE Catalog 2015 [Instruments for Laboratory]	9999