

ACRYLIC RESIN LEVEL

Special Orders
Available

Please request for a quote.

PT 2 Way Flat Level

Special Orders
Available

Special order examples

- Change liquid color to transparent
- Chamfering
- Change mounting hole diameter

The following option fees may be quoted separately.

Sensitivity 0.5mm/m = 0.0286° *PT-23, PT-30 : Sensitivity 1.3mm/m = 0.0764°

PT-50



2 Way Flat Level

Product No.	Size	Vial Size (2 points)	Scale Width (2 points)	Weight	Quantity per Carton	Retail Price	JAN Code
PT-23	16×23×8mm	φ5×10mm	6mm	3g	1	1,400yen	4 993711 581509
PT-30	20×30×10mm	φ6×13mm	6mm	7g	1	1,350yen	4 993711 581516
PT-40	25×40×13mm	φ8×18mm	8mm	15g	1	1,380yen	4 993711 581523
PT-50	35×50×15mm	φ8×25mm	13mm	30g	1	1,400yen	4 993711 581530
PT-70	25×70×15mm	φ8×25mm φ8×18mm	13mm/18mm	30g	1	1,430yen	4 993711 581547

PTh 2 Way Flat Level (With Mounting Holes)

Special Orders
Available

Sensitivity 0.5mm/m = 0.0286° *PTh-30 : Sensitivity 1.3mm/m = 0.0764°

PTh-50



2 Way Flat Level (With Mounting Holes)

Product No.	Size	Vial Size (2 points)	Scale Width (2 points)	Hope Pitch	Hole Diameter (2 points)	Weight	Quantity per Carton	Retail Price	JAN Code
PTh-30	20×30×10mm	φ6×13mm	6mm	13mm	2.7mm	7g	1	1,480yen	4 993711 582223
PTh-40	25×40×13mm	φ8×18mm	8mm	17mm	2.7mm	14g	1	1,510yen	4 993711 582230
PTh-50	35×50×15mm	φ8×25mm	13mm	23mm	3.2mm	29g	1	1,530yen	4 993711 582247
PTh-70	25×70×15mm	φ8×25mm φ8×18mm	13mm/18mm	17mm	2.7mm	29g	1	1,590yen	4 993711 582254

T 2 Way T-shape Flat Level

Special Orders
Available

Sensitivity 0.5mm/m = 0.0286°

*T-30 : Sensitivity 1.3mm/m = 0.0764°

T-50



2 Way T-shape Flat Level

Product No.	Size	Vial Size (2 points)	Scale Width (2 points)	Weight	Quantity per Carton	Retail Price	JAN Code
T-30	20×30×10mm	φ6×13mm	6mm	5g	1	1,430yen	4 993711 581714
T-40	25×40×13mm	φ8×18mm	8mm	10g	1	1,460yen	4 993711 581721
T-50	35×50×15mm	φ8×25mm	13mm	17g	1	1,480yen	4 993711 581738

Th 2 Way T-shape Flat Level (With Mounting Holes)

Special Orders
Available

Sensitivity 0.5mm/m = 0.0286°

*Th-30 : Sensitivity 1.3mm/m = 0.0764°

Th-50



2 Way T-shape Flat Level (With Mounting Holes)

Product No.	Size	Vial Size (2 points)	Scale Width (2 points)	Hole Diameter	Weight	Quantity per Carton	Retail Price	JAN Code
Th-30	20×30×10mm	φ6×13mm	6mm	2.7mm	4g	1	1,510yen	4 993711 582322
Th-40	25×40×13mm	φ8×18mm	8mm	2.7mm	9g	1	1,530yen	4 993711 582339
Th-50	35×50×15mm	φ8×25mm	13mm	3.2mm	16g	1	1,590yen	4 993711 582346

LV Tubular Vial

AK5-13



LV-25



LV-32



LV-6529



LV-1240



LV-40



Tubular Vial

Product No.	Size	Scale Width	Number of Scales	Sensitivity	Weight	Quantity per Carton	Retail Price	JAN Code
AK5-13	φ5×13mm	4mm	2	35'/2mm	0.3g	1	275yen	4 993711 582759
LV-6529	φ6.5×29mm	10mm	2	51'/2mm	0.9g	1	340yen	4 993711 582742
LV-25	φ9.5×25mm	9mm	4	45'/2mm	1.7g	1	390yen	4 993711 582704
LV-32	φ9.5×32mm	12.5mm	4	40'/2mm	1.9g	1	420yen	4 993711 582711
LV-40	φ9.5×40mm	12.5mm	4	35'/2mm	2.8g	1	440yen	4 993711 582728
LV-1240	φ12×40mm	14mm	4	39'/2mm	4g	1	600yen	4 993711 582735

PZ Prism Type Level (With Mounting Plate)

PZ-PTh-45



PZ-Rt-30



PZ-PTh-23 : Sensitivity 1.3mm/m = 0.0764° PZ-Rt-20 : Sensitivity 91'/2mm

PZ-PTh-45 : Sensitivity 0.5mm/m = 0.0286° PZ-Rt-30 : Sensitivity 91'/2mm

For Horizontal Measurement

Prism Type Level (with Mounting Plate)

Product No.	Size	Vial Size	Hope Pitch	Hole Diameter (2 points)	Weight	Quantity per Carton	Retail Price	JAN Code
PZ-PTh-23 (Cross type)	16×23×30.5mm	φ5×10mm (2 points)	22mm	2.6mm	12g	1	4,160yen	4 993711 582612
PZ-PTh-45 (Cross type)	28×45×57.5mm	φ8×20mm (2 points)	34mm	2.6mm	63g	1	4,580yen	4 993711 582629
PZ-Rt-20 (Circular type)	20×20×27.5mm	φ9mm	26mm	2.6mm	13g	1	3,870yen	4 993711 582636
PZ-Rt-30 (Circular type)	30×30×39.5mm	φ18mm	36mm	2.6mm	35g	1	4,000yen	4 993711 582643