

Brass R134a Auto A/C Manifold 70mm Gauge Sets

R134a auto A/C 2-way manifold gauge sets. Hose connections for blue and red are 14mm-M, yellow hose is 1/2" ACME-F. All hoses are designed and crimped for R134a working pressure 600 bursting pressure 3000.



with sight glass

without sight glass



- To order 80mm Gauges with Brass Manifold set, simply place "80" after the item number
- To order manifold gauge sets with rubber protector, simply place "GP" after item number.

Item No.	Length
CT-A536G-AM	36"
CT-A560G-AM	60"
CT-A572G-AM	72"



Item No.	Length
CT-A636G-AM	36"
CT-A660G-AM	60"
CT-A672G-AM	72"

Item No.	Length
CT-A536G-M	36"
CT-A560G-M	60"
CT-A572G-M	72"



Item No.	Length
CT-A636G-M	36"
CT-A660G-M	60"
CT-A672G-M	72"

Item No.	Length
CT-A536G-S	36"
CT-A560G-S	60"
CT-A572G-S	72"



Item No.	Length
CT-A636G-S	36"
CT-A660G-S	60"
CT-A672G-S	72"



- To order manifold gauge sets with Auto-Shut-Off valve, simply place "-AV" after item number.



- To order manifold gauge sets with blow case, simply place "-L" after item number.