

Connector Cables

M17 Series



Features

- M17 Connector type 6-pin / 9-pin / 13-pin models available
- Various cable length (2m, 5m, 10m)
- Available in I-type connector
- Autonics application: Rotary Encoders

Specifications

M17 Connector 6-Pin

Connector 1	Connector 2	Length	Application	Model
M17 (Socket-Female)	6-wire	2 m	Incremental rotary encoders (Totem pole output / NPN open collector output / Voltage output)	CID6S-2
		5 m		CID6S-5
		10 m		CID6S-10
		15 m		CID6S-15

M17 Connector 9-Pin

Connector 1	Connector 2	Length	Application	Model
M17 (Socket-Female)	9 -wire	2 m	Incremental rotary encoders (Line driver output)	CID9S-2
		5 m		CID9S-5
		10 m		CID9S-10

M17 Connector 13-Pin

Connector 1	Connector 2	Length	Application	Model
M17 (Socket-Female)	13-wire	2 m	-	CID13S-2
		5 m		CID13S-5
		10 m		CID13S-10
M17 (Socket-Female)	M17 (Plug-Male)	2 m	-	CID13P-2-SI
		5 m		CID13P-5-SI
		10 m		CID13P-10-SI



View product detail