



HG-3134-

TORQUE

9 0.9N·m
18 1.8N·m

FINISH

BK Black
VN Gray chrome



재질

아연합금

표면처리

흑색도장, 베로아도금

중량

40g

토크

HG-3134-9 : 0.9±0.2N·m

HG-3134-18 : 1.8±0.2N·m

특징

임의의 각도로 도어를 유지

용도

의료기기, 반도체장비 등

Material

Zinc alloy die-cast

Finish

Black powder coated

Gray chrome plated

Weight

40g

Torque

HG-3134-9 : 0.9±0.2N·m

HG-3134-18 : 1.8±0.2N·m

Feature

Holds the door open at any angle

Specific use

semiconductor equipment etc.

