

CC



CC INCH



MODEL(φD-T)

Tube Metric -Thread R			Tube Inch -Thread R	
CC 4×2-01	CC 8×6-02	CC 12×8-04	CC 1/4-01	CC 3/8-01
CC 4×2-02	CC 8×6-03	CC 12×9-02	CC 1/4-02	CC 3/8-02
CC 4×2.5-01	CC 10×6.5-02	CC 12×9-03	CC 1/4-03	CC 3/8-03
CC 6×4-01	CC 10×6.5-03	CC 12×9-04	CC 1/4-04	CC 3/8-04
CC 6×4-02	CC 10×6.5-04	CC 16×12-03	CC 5/16-01	CC 1/2-02
CC 6×4-03	CC 10×8-02	CC 16×12-04	CC 5/16-02	CC 1/2-03
CC 8×5-01	CC 10×8-03	CC 16×13-03	CC 5/16-03	CC 1/2-04
CC 8×5-02	CC 10×8-04	CC 16×13-04	CC 5/16-04	
CC 8×5-03	CC 12×8-02			
CC 8×6-01	CC 12×8-03			

CL



CL INCH



MODEL(φD-T)

Tube Metric -Thread R			Tube Inch -Thread R	
CL 4×2-01	CL 8×6-02	CL 12×8-04	CL 1/4-01	CL 3/8-01
CL 4×2-02	CL 8×6-03	CL 12×9-02	CL 1/4-02	CL 3/8-02
CL 4×2.5-01	CL 10×6.5-02	CL 12×9-03	CL 1/4-03	CL 3/8-03
CL 6×4-01	CL 10×6.5-03	CL 12×9-04	CL 1/4-04	CL 3/8-04
CL 6×4-02	CL 10×6.5-04	CL 16×12-03	CL 5/16-01	CL 1/2-02
CL 6×4-03	CL 10×8-02	CL 16×12-04	CL 5/16-02	CL 1/2-03
CL 8×5-01	CL 10×8-03	CL 16×13-03	CL 5/16-03	CL 1/2-04
CL 8×5-02	CL 10×8-04	CL 16×13-04	CL 5/16-04	
CL 8×5-03	CL 12×8-02			
CL 8×6-01	CL 12×8-03			

CT



MODEL(φD-T)

Tube Metric -Thread R	
CT 4×2-01	CT 10×6.5-02
CT 4×2-02	CT 10×6.5-03
CT 4×2.5-01	CT 10×6.5-04
CT 6×4-01	CT 10×8-02
CT 6×4-02	CT 10×8-03
CT 6×4-03	CT 10×8-04
CT 8×5-01	CT 12×8-02
CT 8×5-02	CT 12×8-03
CT 8×5-03	CT 12×8-04
CT 8×6-01	CT 12×9-02
CT 8×6-02	CT 12×9-03
CT 8×6-03	CT 12×9-04

CUC



MODEL(φD)

Tube Metric	Tube Inch
CUC 4×2	CUC 1/4
CUC 4×2.5	CUC 3/8
CUC 6×4	CUC 1/2
CUC 8×5	
CUC 8×6	
CUC 10×6.5	
CUC 10×8	
CUC 12×8	
CUC 12×9	

CUC INCH

