

VGA with Audio

VESA-DDC Plug and Play compliant

Type	Model	Length (m)
HD-15 (M) 3.5mm TRS	A1VGA005	0.5
HD-15 (M) 3.5mm TRS	A1VGA0075	0.75
	A1VGA01	1
	A1VGA015	1.5
	A1VGA02	2
	A1VGA03	3
	A1VGA05	5
	A1VGA10	10

A: 20cm (A1VGA005)
60cm (others)

BLK Screws: #4-40 UNC inch thread

3 RCA Video & Audio NEW

Type	Model	Length (m)
RCA - RCA	3RCS003	0.3
	3RCS005	0.5
	3RCS01	1
	3RCS015	1.5
	3RCS02	2
	3RCS03	3
	3RCS05	5
	3RCS10	10
	3RCS15	15
	3RCS20	20
	3RCS30	30

BLK

2 RCA Stereo Audio NEW

Type	Model	Length (m)
RCA - RCA	2RCS003	0.3
	2RCS005	0.5
	2RCS01	1
	2RCS015	1.5
	2RCS02	2
	2RCS03	3
	2RCS05	5
	2RCS10	10
	2RCS15	15
	2RCS20	20
	2RCS30	30

BLK