

PP サニタリーパイプ

材質 304/316L



SIZE	D	C	t
8A	13.8	10.5	1.65
10A	17.3	14.0	1.65
15A	21.7	17.5	2.1
1S	25.4	23.0	1.2
1.25S	31.8	29.4	1.2
1.5S	38.1	35.7	1.2
2S	50.8	47.8	1.5
2.5S	63.5	59.5	2.0
3S	76.3	72.3	2.0
3.5S	89.1	85.1	2.0
4S	101.6	97.6	2.0

寸法表

切断販売も可能です。

EL-W 溶接90°エルボ

材質 304/316L/※チタン



SIZE	D	A
1S	25.4	34
1.25S	31.8	38
1.5S	38.1	49
2S	50.8	61
2.5S	63.5	84
3S	76.3	89
3.5S	89.1	104
4S	101.6	133.4

寸法表

ロングタイプもあります。

EQ-W 溶接45°エルボ

材質 304/316L



SIZE	D	A
1S	25.4	15.8
1.25S	31.8	15.7
1.5S	38.1	23.7
2S	50.8	31.6
2.5S	63.5	42.0
3S	76.3	52.6
3.5S	89.1	42.9
4S	101.6	73.6

寸法表

TE(LTE)-W 溶接チーズ(ローネックチーズ)

材質 304/316L/※チタン



SIZE	D	A	B
1S	25.4	34	14
1.25S	31.8	38	※
1.5S	38.1	49	21
2S	50.8	61	28
2.5S	63.5	84	34
3S	76.3	89	40.5
3.5S	89.1	104	※
4S	101.6	133.4	※

寸法表

異径タイプもあります。

RC(RE)-W 溶接レデューサー(同心・偏心)

材質 304/316L/※チタン(同心のみ)



RC



RE

寸法表

SIZE	D1	D2	L	SIZE	D1	D2	L
1.25S×1S	31.8	25.4	67	3S×2.5S	76.3	63.5	67
1.5S×1.25S	38.1	31.8	67	3S×2S	76.3	50.8	67
1.5S×1S	38.1	25.4	67	3S×1.5S	76.3	38.1	67
2S×1.5S	50.8	38.1	67	3.5S×3S	89.1	76.3	67
2S×1.25S	50.8	31.8	67	3.5S×2.5S	89.1	63.5	67
2S×1S	50.8	25.4	67	3.5S×2S	89.1	50.8	67
2.5S×2S	63.5	50.8	67	4S×3.5S	101.6	89.1	102
2.5S×1.5S	63.5	38.1	67	4S×3S	101.6	76.3	102
2.5S×1.25S	63.5	31.8	67	4S×2.5S	101.6	63.5	102
2.5S×1S	63.5	25.4	67	4S×2S	101.6	50.8	102

XS-W 溶接クロス

材質 304/316L



SIZE	D	A
1S	25.4	34
1.25S	31.8	38
1.5S	38.1	49
2S	50.8	61
2.5S	63.5	84
3S	76.3	89
3.5S	89.1	104
4S	101.6	133.4

寸法表

EU-W 溶接180°ベンド

材質 304/316L



SIZE	D	A	B
1.5S	38.1	152.4	76.2
2S	50.8	152.4	76.2
2.5S	63.5	190.6	95.3
3S	76.3	254	127
4S	101.6	254	127

寸法表

WA-H 溶接ホースアダプター

材質 304/316L



SIZE	D	L
1S	25.4	60
1.25S	31.8	※
1.5S	38.1	80
2S	50.8	80
2.5S	63.5	80
3S	76.3	80
3.5S	89.1	※
4S	101.6	※

寸法表

HC-W 溶接半球キャップ

材質 304/316L



皿型もあります。

SIZE	D	A	t
1S	25.4	12.7	1.2
1.5S	38.1	19.05	1.2
2S	50.8	25.4	1.5
2.5S	63.5	31.75	2.0
3S	76.3	38.15	2.0
3.5S	89.1	44.55	2.0
4S	101.6	50.8	2.0

寸法表

※は別途お問い合わせください