

DDK05スラストワッシャー寸法表

部品番号の表示方法



K5T 06

Parts No.でご指示ください

(単位 mm)

呼び内径	部品番号	内径	外径	肉厚	ノック穴		ハウジングくぼみの深さ	
					直径	P. C. D		
6	K5T06	8 ^{+0.25} ₀	16 ⁰ _{-0.25}	1.5 ^{-0.03} _{-0.08}	1.100 ^{+0.20} ₀	12 ^{±0.12}	1.0 ^{+0.20} _{-0.05}	
8	K5T08	10 [°]	18 [°]			14 [°]		
10	K5T10	12 [°]	24 [°]			1.625 ^{+0.25} ₀		18 [°]
12	K5T12	14 [°]	26 [°]					20 [°]
14	K5T14	16 [°]	30 [°]		2.125 ^{+0.25} ₀	23 [°]		
16	K5T16	18 [°]	32 [°]			25 [°]		
18	K5T18	20 [°]	36 [°]		3.125 ^{+0.25} ₀	28 [°]		
20	K5T20	22 [°]	38 [°]			30 [°]		
22	K5T22	24 [°]	42 [°]			33 [°]		
24	K5T24	26 [°]	44 [°]			35 [°]		
25	K5T25	28 [°]	48 [°]		4.125 ^{+0.25} ₀	38 [°]		
30	K5T30	32 [°]	54 [°]			43 [°]		
35	K5T35	38 [°]	62 [°]			50 [°]		
40	K5T40	42 [°]	66 [°]			54 [°]		
45	K5T45	48 [°]	74 [°]	2.0 ^{-0.03} _{-0.08}	61 [°]	1.5 ^{+0.20} _{-0.05}		
50	K5T50	52 [°]	78 [°]		65 [°]			

