



50AF															
N						S			H			L			
DBN 52Nb	DBN 53Nb	DBN 54Nb	DBN 52S	DBN 53S	DBN 54S	DBS 52Sd	DBS 53Sd	DBS 54Sd	DBH 52S	DBH 53S	DBH 54S	DBL 52S	DBL 53S	DBL 54S	
2	3	4	2	3	4	2	3	4	2	3	4	2	3	4	
5,10,15,20,30,40,50			15,20,30,40,50			15,20,30,40,50			40,50			(15,20,30)40,50			
690			690			690			690			690			
250		-	500			500			500			500			
750			750			750			750			750			
6			8			8			8			6			
5			2.5			7.5			10			35			
7.5			7.5			14			35			42			
14			14			26			50			65			
14			18			30			50			65			
25			30			50			100			125			
-	-	-	-	5	5	-	10	10	-	30	30	-	40	40	
2.5	2.5	-	5	-	-	10	-	-	30	-	-	40	-	-	
50			100			100			100			50			
Hydraulic Magnetic (ODP)			Thermal Magnetic			Thermal Magnetic			Thermal Magnetic			Thermal Magnetic			
-			[0.8-0.9-1.0]×In			[0.8-0.9-1.0]×In			[0.8-0.9-1.0]×In			-			
-			-			-			-			-			
[8-12]×In			[8-12]×In			[8-12]×In			[8-12]×In			[8-12]×In			
50×130×60			50×130×60			50×130×60			60×155×60			90×155×86			
75×130×60			75×130×60			75×130×60			90×155×60						
100×130×60			100×130×60			100×130×60			120×155×60			120×155×86			
○			○			○			○			○			
-			-			-			-			-			
Screw			Screw			Screw			Screw			Screw			
-			○			○			○			○			
-			○			○			○			○			
-			○			○			○			○			
-			-			-			-			-			
○			○			○			○			○			
○			○			○			○			○			
-			-			-			-			-			
○			○			○			○			○			
○			○			○			○			○			
-			○			○			-			-			
-			○			○			-			-			
-			-			○			-			-			
15-50A			○			○			○			-			
15-50A			○			○			○			-			
-			-			○			-			-			
15-50A			○			○			○			40,50A			