



630AF									
N			S			L			
DBN 632S	DBN 633S	DBN 634S	DBS 632S	DBS 633S	DBS 634S	DBL 632S	DBL 633S	DBL 634S	
2	3	4	2	3	4	2	3	4	
500,630			500,630			500,630			
690			690			690			
500			500			500			
750			750			750			
8			8			8			
5			8			14			
18			35			65			
42			65			85			
45			75			100			
60			85			125			
-	10	10	-	20	20	-	40	40	
10	-	-	20	-	-	40	-	-	
100			100			100			
Thermal Magnetic			Thermal Magnetic			Thermal Magnetic			
(0.8-0.9-1.0)×In			(0.8-0.9-1.0)×In			(0.8-0.9-1.0)×In			
[5-6-7-8-9-10]×In			[5-6-7-8-9-10]×In			-			
[8-12]×In			[8-12]×In			[8-12]×In			
140×257×103			140×257×103			140×257×103			
184×257×103			184×257×103			184×257×103			
○			○			○			
-			-			-			
Screw			Screw			Screw			
○			○			○			
○			○			○			
○			○			○			
-			-			-			
-			-			-			
-			-			-			
-			-			-			
○			○			○			
○			○			○			
○			○			○			
-			-			-			
-			-			-			
○			○			-			