

## LHS-7D / LHS-8D / LHS-9D / LHS-9ZD

## DOOR HOLDER SET (mm. size / inch size)

SURFACE TREATMENT : EL/ARMOUR plated / PACKAGE : Slide blister pack



LHS-9D



LHS-9ZD



LHS-8D



LHS-7D

Item No.	Pcs.	H								Inner	D×W×H	g	
LHS-7D	7	1.5	2	2.5	3	4	5	6		10	255×153×93	1,761	
LHS-8D	8	1.5	2	2.5	3	4	5	6	8	5	279×91×99	1,514	
LHS-9D	9	1.5	2	2.5	3	4	5	6	8	10	5	320×103×114	2,566
LHS-9ZD	9	1/16	5/64	3/32	1/8	5/32	3/16	1/4	5/16	3/8	5	320×103×114	2,478


## LH-\*

## INDIVIDUAL (mm. size / inch size)

SURFACE TREATMENT : EL/ARMOUR plated / PACKAGE : Bulk pack



LH-6



Item No.	H	L1	L2	Inner	D×W×H	g
LH-1.5	1.5	16	79	20	162×68×35	60
LH-2	2	17	95	20	162×68×35	90
LH-2.5	2.5	18	110	20	162×68×35	140
LH-3	3	20	126	20	162×68×35	205
LH-4	4	25	142	20	162×68×35	390
LH-5	5	28	160	20	202×65×32	665
LH-6	6	32	180	20	226×75×32	1,070
LH-8	8	36	200	10	226×75×32	1,060
LH-10	10	40	224	10	250×90×38	1,845
LH-12	12	45	250	4	275×78×35	1,205
LH-14	14	55	280	4	302×90×35	1,840
LH-17	17	60	320	4	347×102×43	3,080
LH-19	19 (3/4")	70	360	4	411×96×47	4,135

Item No.	H	L1	L2	Inner	D×W×H	g
LH-1/16	1/16"	15	79	20	162×68×35	68
LH-5/64	5/64"	17	93	20	162×68×35	88
LH-3/32	3/32"	18	108	20	162×68×35	125
LH-1/8	1/8"	20	127	20	162×68×35	230
LH-5/32	5/32"	25	140	20	162×68×35	380
LH-3/16	3/16"	28	158	20	202×65×32	595
LH-1/4	1/4"	32	178	20	226×75×32	1,180
LH-5/16	5/16"	36	198	10	226×75×32	1,035
LH-3/8	3/8"	40	222	10	250×90×38	1,665

※Pack packaging is also available.

※Pack packaging is also available except for LH-17 to LH-19.