



Elesa 표준				주요 규격			나사 스템		렌치	최대 적정 하중		q	
LM.AC		LM.SST-AC		D	L	l1	d	l	s	[N]	[N]#	g	g#
코드	설명	코드	설명										
401623	LM.25 M8x40-AC	402623	LM.25-SST M8x40-AC	25	60.5	20.5	M8	40	12	14000	7000	65	67
401624	LM.25 M8x50-AC	402624	LM.25-SST M8x50-AC	25	70.5	20.5	M8	50	12	14000	7000	55	55
401626	LM.25 M8x63-AC	402626	LM.25-SST M8x63-AC	25	83.5	20.5	M8	63	12	14000	7000	69	71
401630	LM.32 M8x40-AC	402630	LM.32-SST M8x40-AC	32	64.5	24.5	M8	40	12	14000	7000	52	52
401631	LM.32 M8x50-AC	402631	LM.32-SST M8x50-AC	32	74.5	24.5	M8	50	12	14000	7000	57	57
401632	LM.32 M8x63-AC	402632	LM.32-SST M8x63-AC	32	87.5	24.5	M8	63	12	14000	7000	67	67
401633	LM.32 M10x50-AC	402633	LM.32-SST M10x50-AC	32	74.5	24.5	M10	50	15	23000	11000	106	109
-	-	402634	LM.32-SST M10x63-AC	32	87.5	24.5	M10	63	15	-	11000	-	172
401636	LM.32 M10x80-AC	402636	LM.32-SST M10x80-AC	32	104.5	24.5	M10	80	15	23000	11000	120	124
401640	LM.40 M10x50-AC	402640	LM.40-SST M10x50-AC	40	77.5	27.5	M10	50	15	23000	11000	157	157
401641	LM.40 M10x63-AC	402641	LM.40-SST M10x63-AC	40	90.5	27.5	M10	63	15	23000	11000	165	165
401642	LM.40 M10x80-AC	402642	LM.40-SST M10x80-AC	40	107.5	27.5	M10	80	15	23000	11000	172	172
401643	LM.40 M12x63-AC	402643	LM.40-SST M12x63-AC	40	90.5	27.5	M12	63	17	33000	16000	185	185
-	-	402644	LM.40-SST M12x80-AC	40	107.5	27.5	M12	80	17	-	16000	-	190
401646	LM.40 M12x100-AC	402646	LM.40-SST M12x100-AC	40	127.5	27.5	M12	100	17	33000	16000	210	214
401650	LM.50 M10x50-AC	402650	LM.50-SST M10x50-AC	50	79.5	29.5	M10	50	15	23000	11000	207	207
401651	LM.50 M10x63-AC	402651	LM.50-SST M10x63-AC	50	92.5	29.5	M10	63	15	23000	11000	215	215
401652	LM.50 M10x80-AC	402652	LM.50-SST M10x80-AC	50	109.5	29.5	M10	80	15	23000	11000	222	222
401653	LM.50 M12x63-AC	402653	LM.50-SST M12x63-AC	50	92.5	29.5	M12	63	17	33000	16000	260	260
-	-	402654	LM.50-SST M12x80-AC	50	109.5	29.5	M12	80	17	-	16000	-	270
401656	LM.50 M12x100-AC	402656	LM.50-SST M12x100-AC	50	129.5	29.5	M12	100	17	33000	16000	285	294
401660	LM.60 M12x63-AC	402660	LM.60-SST M12x63-AC	60	100.5	37.5	M12	63	17	33000	16000	440	440
401661	LM.60 M12x80-AC	402661	LM.60-SST M12x80-AC	60	117.5	37.5	M12	80	17	33000	16000	465	465
401662	LM.60 M12x100-AC	402662	LM.60-SST M12x100-AC	60	137.5	37.5	M12	100	17	33000	16000	500	500
401663	LM.60 M16x80-AC	402663	LM.60-SST M16x80-AC	60	117.5	37.5	M16	80	24	62000	30000	490	505
401666	LM.60 M16x125-AC	402666	LM.60-SST M16x125-AC	60	162.5	37.5	M16	125	24	62000	30000	550	566
401671	LM.60 M20x98-AC	402671	LM.60-SST M20x98-AC	60	135.5	37.5	M20	98	24	95000	45000	550	550
401673	LM.60 M20x138-AC	402673	LM.60-SST M20x138-AC	60	175.5	37.5	M20	138	24	95000	45000	580	580
401676	LM.60 M20x158-AC	402676	LM.60-SST M20x158-AC	60	195.5	37.5	M20	158	24	95000	45000	610	610

LM.SST-AC용 값.