

Elesa 표준				주요 규격						나사 스템		최대 적정 하중
코드	설명	코드	설명	D	L	l1	l2	s	s1	d	l	[N]
404061	LMP.50-M10-50	404561	LMP.50-SST-M10-50	50	61	11	2,5	17	-	M10	50	10000
404063	LMP.50-M10-60	404563	LMP.50-SST-M10-60	50	71	11	2,5	17	-	M10	60	10000
404065	LMP.50-M10-80	404565	LMP.50-SST-M10-80	50	91	11	2,5	17	-	M10	80	10000
404067	LMP.50-M10-100	404567	LMP.50-SST-M10-100	50	111	11	2,5	17	-	M10	100	10000
404071	LMP.50-M12-60	404571	LMP.50-SST-M12-60	50	71	11	2,5	17	-	M12	60	10000
404073	LMP.50-M12-80	404573	LMP.50-SST-M12-80	50	91	11	2,5	17	-	M12	80	10000
404075	LMP.50-M12-100	404575	LMP.50-SST-M12-100	50	111	11	2,5	17	-	M12	100	10000
404077	LMP.50-M12-125	404577	LMP.50-SST-M12-125	50	136	11	2,5	17	-	M12	125	10000
404081	LMP.50-M16-75	404581	LMP.50-SST-M16-75	50	92	17	2,5	12	8	M16	75	10000
404083	LMP.50-M16-100	404583	LMP.50-SST-M16-100	50	117	17	2,5	12	8	M16	100	10000
404085	LMP.50-M16-125	404585	LMP.50-SST-M16-125	50	142	17	2,5	12	8	M16	125	10000
404087	LMP.50-M16-150	404587	LMP.50-SST-M16-150	50	167	17	2,5	12	8	M16	150	10000
404111	LMP.60-M10-50	404611	LMP.60-SST-M10-50	60	61	11	2,5	17	-	M10	50	10000
404113	LMP.60-M10-60	404613	LMP.60-SST-M10-60	60	71	11	2,5	17	-	M10	60	10000
404115	LMP.60-M10-80	404615	LMP.60-SST-M10-80	60	91	11	2,5	17	-	M10	80	10000
404117	LMP.60-M10-100	404617	LMP.60-SST-M10-100	60	111	11	2,5	17	-	M10	100	10000
404121	LMP.60-M12-60	404621	LMP.60-SST-M12-60	60	71	11	2,5	17	-	M12	60	10000
404123	LMP.60-M12-80	404623	LMP.60-SST-M12-80	60	91	11	2,5	17	-	M12	80	10000
404125	LMP.60-M12-100	404625	LMP.60-SST-M12-100	60	111	11	2,5	17	-	M12	100	10000
404127	LMP.60-M12-125	404627	LMP.60-SST-M12-125	60	136	11	2,5	17	-	M12	125	10000
404131	LMP.60-M16-75	404631	LMP.60-SST-M16-75	60	92	17	2,5	12	8	M16	75	12000
404133	LMP.60-M16-100	404633	LMP.60-SST-M16-100	60	117	17	2,5	12	8	M16	100	12000
404135	LMP.60-M16-125	404635	LMP.60-SST-M16-125	60	142	17	2,5	12	8	M16	125	12000
404137	LMP.60-M16-150	404637	LMP.60-SST-M16-150	60	167	17	2,5	12	8	M16	150	12000
404151	LMP.80-M10-50	404651	LMP.80-SST-M10-50	80	61	11	3	17	-	M10	50	10000
404153	LMP.80-M10-60	404653	LMP.80-SST-M10-60	80	71	11	3	17	-	M10	60	10000
404155	LMP.80-M10-80	404655	LMP.80-SST-M10-80	80	91	11	3	17	-	M10	80	10000
404157	LMP.80-M10-100	404657	LMP.80-SST-M10-100	80	111	11	3	17	-	M10	100	10000
404161	LMP.80-M12-60	404661	LMP.80-SST-M12-60	80	71	11	3	17	-	M12	60	10000
404163	LMP.80-M12-80	404663	LMP.80-SST-M12-80	80	91	11	3	17	-	M12	80	10000
404165	LMP.80-M12-100	404665	LMP.80-SST-M12-100	80	111	11	3	17	-	M12	100	10000
404167	LMP.80-M12-125	404667	LMP.80-SST-M12-125	80	136	11	3	17	-	M12	125	10000
404171	LMP.80-M16-75	404671	LMP.80-SST-M16-75	80	92	17	3	12	8	M16	75	12000
404173	LMP.80-M16-100	404673	LMP.80-SST-M16-100	80	117	17	3	12	8	M16	100	12000
404175	LMP.80-M16-125	404675	LMP.80-SST-M16-125	80	142	17	3	12	8	M16	125	12000
404177	LMP.80-M16-150	404677	LMP.80-SST-M16-150	80	167	17	3	12	8	M16	150	12000
404181	LMP.80-M20-75	404681	LMP.80-SST-M20-75	80	93	18	3	15	10	M20	75	15000
404183	LMP.80-M20-100	404683	LMP.80-SST-M20-100	80	118	18	3	15	10	M20	100	15000
404185	LMP.80-M20-125	404685	LMP.80-SST-M20-125	80	143	18	3	15	10	M20	125	15000
404187	LMP.80-M20-150	404687	LMP.80-SST-M20-150	80	168	18	3	15	10	M20	150	15000
404193	LMP.80-M24-100	404693	LMP.80-SST-M24-100	80	121	21	3	19	12	M24	100	18000
404195	LMP.80-M24-125	404695	LMP.80-SST-M24-125	80	146	21	3	19	12	M24	125	18000
404197	LMP.80-M24-150	404697	LMP.80-SST-M24-150	80	171	21	3	19	12	M24	150	18000