

Elesa 표준				주요 규격						나사 스템		최대 적정 하중
코드	설명	코드	설명	D	L	l1	l2	s	s1	d	l	[N]
404261	LMP.50-M10-50-TR	404761	LMP.50-SST-M10-50-TR	50	63	13	2,5	17	-	M10	50	10000
404263	LMP.50-M10-60-TR	404763	LMP.50-SST-M10-60-TR	50	73	13	2,5	17	-	M10	60	10000
404265	LMP.50-M10-80-TR	404765	LMP.50-SST-M10-80-TR	50	93	13	2,5	17	-	M10	80	10000
404267	LMP.50-M10-100-TR	404767	LMP.50-SST-M10-100-TR	50	113	13	2,5	17	-	M10	100	10000
404271	LMP.50-M12-60-TR	404771	LMP.50-SST-M12-60-TR	50	73	13	2,5	17	-	M12	60	10000
404273	LMP.50-M12-80-TR	404773	LMP.50-SST-M12-80-TR	50	93	13	2,5	17	-	M12	80	10000
404275	LMP.50-M12-100-TR	404775	LMP.50-SST-M12-100-TR	50	113	13	2,5	17	-	M12	100	10000
404277	LMP.50-M12-125-TR	404777	LMP.50-SST-M12-125-TR	50	138	13	2,5	17	-	M12	125	10000
404281	LMP.50-M16-75-TR	404781	LMP.50-SST-M16-75-TR	50	94	19	2,5	12	8	M16	75	10000
404283	LMP.50-M16-100-TR	404783	LMP.50-SST-M16-100-TR	50	119	19	2,5	12	8	M16	100	10000
404285	LMP.50-M16-125-TR	404785	LMP.50-SST-M16-125-TR	50	144	19	2,5	12	8	M16	125	10000
404287	LMP.50-M16-150-TR	404787	LMP.50-SST-M16-150-TR	50	169	19	2,5	12	8	M16	150	10000
404311	LMP.60-M10-50-TR	404811	LMP.60-SST-M10-50-TR	60	63	13	2,5	17	-	M10	50	10000
404313	LMP.60-M10-60-TR	404813	LMP.60-SST-M10-60-TR	60	73	13	2,5	17	-	M10	60	10000
404315	LMP.60-M10-80-TR	404815	LMP.60-SST-M10-80-TR	60	93	13	2,5	17	-	M10	80	10000
404317	LMP.60-M10-100-TR	404817	LMP.60-SST-M10-100-TR	60	113	13	2,5	17	-	M10	100	10000
404321	LMP.60-M12-60-TR	404821	LMP.60-SST-M12-60-TR	60	73	13	2,5	17	-	M12	60	10000
404323	LMP.60-M12-80-TR	404823	LMP.60-SST-M12-80-TR	60	93	13	2,5	17	-	M12	80	10000
404325	LMP.60-M12-100-TR	404825	LMP.60-SST-M12-100-TR	60	113	13	2,5	17	-	M12	100	10000
404327	LMP.60-M12-125-TR	404827	LMP.60-SST-M12-125-TR	60	138	13	2,5	17	-	M12	125	10000
404331	LMP.60-M16-75-TR	404831	LMP.60-SST-M16-75-TR	60	94	19	2,5	12	8	M16	75	12000
404333	LMP.60-M16-100-TR	404833	LMP.60-SST-M16-100-TR	60	119	19	2,5	12	8	M16	100	12000
404335	LMP.60-M16-125-TR	404835	LMP.60-SST-M16-125-TR	60	144	19	2,5	12	8	M16	125	12000
404337	LMP.60-M16-150-TR	404837	LMP.60-SST-M16-150-TR	60	169	19	2,5	12	8	M16	150	12000
404351	LMP.80-M10-50-TR	404851	LMP.80-SST-M10-50-TR	80	63	13	3	17	-	M10	50	10000
404353	LMP.80-M10-60-TR	404853	LMP.80-SST-M10-60-TR	80	73	13	3	17	-	M10	60	10000
404355	LMP.80-M10-80-TR	404855	LMP.80-SST-M10-80-TR	80	93	13	3	17	-	M10	80	10000
404357	LMP.80-M10-100-TR	404857	LMP.80-SST-M10-100-TR	80	113	13	3	17	-	M10	100	10000
404361	LMP.80-M12-60-TR	404861	LMP.80-SST-M12-60-TR	80	73	13	3	17	-	M12	60	10000
404363	LMP.80-M12-80-TR	404863	LMP.80-SST-M12-80-TR	80	93	13	3	17	-	M12	80	10000
404365	LMP.80-M12-100-TR	404865	LMP.80-SST-M12-100-TR	80	113	13	3	17	-	M12	100	10000
404367	LMP.80-M12-125-TR	404867	LMP.80-SST-M12-125-TR	80	138	13	3	17	-	M12	125	10000
404371	LMP.80-M16-75-TR	404871	LMP.80-SST-M16-75-TR	80	94	19	3	12	8	M16	75	12000
404373	LMP.80-M16-100-TR	404873	LMP.80-SST-M16-100-TR	80	119	19	3	12	8	M16	100	12000
404375	LMP.80-M16-125-TR	404875	LMP.80-SST-M16-125-TR	80	144	19	3	12	8	M16	125	12000
404377	LMP.80-M16-150-TR	404877	LMP.80-SST-M16-150-TR	80	169	19	3	12	8	M16	150	12000
404381	LMP.80-M20-75-TR	404881	LMP.80-SST-M20-75-TR	80	95	20	3	15	10	M20	75	15000
404383	LMP.80-M20-100-TR	404883	LMP.80-SST-M20-100-TR	80	120	20	3	15	10	M20	100	15000
404385	LMP.80-M20-125-TR	404885	LMP.80-SST-M20-125-TR	80	145	20	3	15	10	M20	125	15000
404387	LMP.80-M20-150-TR	404887	LMP.80-SST-M20-150-TR	80	170	20	3	15	10	M20	150	15000
404393	LMP.80-M24-100-TR	404893	LMP.80-SST-M24-100-TR	80	123	23	3	19	12	M24	100	18000
404395	LMP.80-M24-125-TR	404895	LMP.80-SST-M24-125-TR	80	148	23	3	19	12	M24	125	18000
404397	LMP.80-M24-150-TR	404897	LMP.80-SST-M24-150-TR	80	173	23	3	19	12	M24	150	18000