



Elesa 표준		주요 치수									온도		q
코드	사양	f	d	A	B	C	L	e	m	r	°C	°F	g
11341	HCX.76-M10	76	M10	22	16	27	107	40	18	15.5	-	-	87
11346	HCX.76/T-M10	76	M10	22	16	27	107	40	18	15.5	20÷100	68÷210	87
11349	HCX.127-M10	127	M10	23	18	31	161	80	23	17	-	-	138
11354	HCX.127/T-M10	127	M10	23	18	31	161	80	23	17	0÷100	32÷210	138
11351	HCX.127-M12	127	M12	23	18	31	161	80	23	17	-	-	138
11356	HCX.127/T-M12	127	M12	23	18	31	161	80	23	17	0÷100	32÷210	138
11361	HCX.254-M12	254	M12	21	18	35	291	203	26	18.5	-	-	185
11366	HCX.254/T-M12	254	M12	21	18	35	291	203	26	18.5	0÷100	32÷210	185