



# FITTING

## MBT

### MALE BRANCH TEE

両口チーズ(オス)



(METRIC)

(Unit:mm)

TUBE O.D. T	THREADS PT or NPT	PART. No.	A	B	C	D	E	F	G	H	J	K
3	1/8	MBT-3-1	25	10	20	15	2.5	5	12	18	36	50
4	1/8	MBT-4-1	28.3	10	21	15.3	3.5	5	14	21	42	56.6
6	1/8	MBT-6-1	28.4	10	21	15.4	5	5	14	21	42	56.6
6	1/4	MBT-6-2	29.4	12	23	15.4	5	6	14	22	44	58.8
8	1/8	MBT-8-1	29.8	10	22	16.8	6	5	15.87	22	44	59.6
8	1/4	MBT-8-2	29.8	12	23	16.8	6	6	15.87	22	44	59.6
10	1/4	MBT-10-2	31.7	12	25	18.7	8	6	19	23	46	63.4
10	3/8	MBT-10-3	31.7	13	25	18.7	8	8	19	23	46	63.4
12	3/8	MBT-12-3	38.3	14	30	22.8	10	8	23	27.5	55	76.6
12	1/2	MBT-12-4	38.3	17	33	22.8	10	10	23	27.5	55	76.6

※管外径5φも製作しております。

(INCHES)

TUBE O.D. T	THREADS PT or NPT	PART. No.	A	B	C	D	E	F	G	H	J	K
1/8": 3.18	1/8	MBT-01-1	25	10	20	15	2.5	5	12	18	36	50
1/4": 6.35	1/8	MBT-02-1	28.4	10	21	15.4	5	5	14	21	42	56.8
1/4": 6.35	1/4	MBT-02-2	29.4	12	23	15.4	5	6	14	22	44	56.8
5/16": 7.94	1/8	MBT-025-1	29.8	10	23	16.8	6	5	15.87	22	44	59.6
5/16": 7.94	1/4	MBT-025-2	29.8	12	23	16.8	6	6	15.87	22	44	59.6
3/8": 9.53	1/4	MBT-03-2	31.3	12	25	17.8	7	6	17.46	23	46	62.6
3/8": 9.53	3/8	MBT-03-3	31.3	13	25	17.8	7	8	17.46	23	46	62.6
1/2": 12.7	3/8	MBT-04-3	38.3	14	30	22.8	10	8	23	27.5	55	76.6
1/2": 12.7	1/2	MBT-04-4	38.3	17	33	22.8	10	10	23	27.5	55	76.6


A.D.:FINGER TIGHT±0.5mm (about)

※管外径5φも製作しております。

## MRT

### MALE RUN TEE

サービステー(オス)



(METRIC)

(Unit:mm)

TUBE O.D. T	THREADS PT or NPT	PART. No.	A	B	D	E	F	G	H	J	K
3	1/8	MRT-3-1	25	10	15	2.5	5	12	18	38	45
4	1/8	MRT-4-1	28.3	10	15.3	3.5	5	14	21	42	49.3
6	1/8	MRT-6-1	28.4	10	15.4	5	5	14	21	42	49.4
6	1/4	MRT-6-2	29.4	12	15.4	5	6	14	22	45	52.4
8	1/8	MRT-8-1	29.8	10	16.8	6	5	15.87	22	44	51.8
8	1/4	MRT-8-2	29.8	12	16.8	6	6	15.87	22	45	52.8
10	1/4	MRT-10-2	31.7	12	18.7	8	6	19	23	48	56.7
10	3/8	MRT-10-3	31.7	13	18.7	8	8	19	23	48	56.7
12	3/8	MRT-12-3	38.3	14	22.8	10	8	23	27.5	57.5	67.8
12	1/2	MRT-12-4	38.3	17	22.8	10	10	23	27.5	60.5	71.3

※管外径5φも製作しております。

(INCHES)

TUBE O.D. T	THREADS PT or NPT	PART. No.	A	B	D	E	F	G	H	J	K
1/8": 3.18	1/8	MRT-01-1	25	10	15	2.5	5	12	18	38	45
1/4": 6.35	1/8	MRT-02-1	28.4	10	15.4	5	5	14	21	42	49.4
1/4": 6.35	1/4	MRT-02-2	29.4	12	15.4	5	6	14	22	45	52.4
5/16": 7.94	1/8	MRT-025-1	29.8	10	16.8	6	5	15.87	22	44	51.8
5/16": 7.94	1/4	MRT-025-2	29.8	12	16.8	6	6	15.87	22	45	52.8
3/8": 9.53	1/4	MRT-03-2	31.3	12	17.8	7	6	17.46	23	48	56.3
3/8": 9.53	3/8	MRT-03-3	31.3	13	17.8	7	8	17.46	23	48	56.3
1/2": 12.7	3/8	MRT-04-3	38.3	14	22.8	10	8	23	27.5	57.5	68.3
1/2": 12.7	1/2	MRT-04-4	38.3	17	22.8	10	10	23	27.5	60.5	71.3

A.D.:FINGER TIGHT±0.5mm (about)

※管外径5φも製作しております。