



# FITTING

## FC

### FEMALE CONNECTOR

圧力計ユニオン



### (METRIC)

TUBE O.D. T	THREADS PT or NPT	PART. No.	A	B	C	D	E	F	G	H
2	1/8	FC-2-1	28.5	12	11.9	9.5	1.3	14	8	24
2	1/4	FC-2-2	28.5	15	11.9	9.5	1.3	17	8	17
3	1/8	FC-3-1	33	12	16	15	2.5	14	12	26
3	1/4	FC-3-2	36	15	16	15	2.5	17	12	29
4	1/8	FC-4-1	35.3	12	18.3	15.3	3.5	14	14	28
4	1/4	FC-4-2	36.3	15	18.3	15.3	3.5	17	14	29
6	1/8	FC-6-1	35.4	12	18.4	15.4	5	14	14	28
6	1/4	FC-6-2	36.4	15	18.4	15.4	5	17	14	29
6	3/8	FC-6-3	38.4	16	18.4	15.4	5	22	14	31
6	1/2	FC-6-4	40.4	19	18.4	15.4	5	26	14	33
8	1/4	FC-8-2	36.8	15	18.8	16.8	6	17	15.87	29
8	3/8	FC-8-3	38.8	16	18.8	16.8	6	22	15.87	31
8	1/2	FC-8-4	40.8	19	18.8	16.8	6	26	15.87	33
10	1/4	FC-10-2	38.7	15	20.7	18.7	8	17	19	30
10	3/8	FC-10-3	40.7	16	20.7	18.7	8	22	19	32
10	1/2	FC-10-4	42.7	19	20.7	18.7	8	26	19	34
12	1/4	FC-12-2	40.8	15	22.8	22.8	10	22	23	30
12	3/8	FC-12-3	42.8	16	22.8	22.8	10	22	23	32
12	1/2	FC-12-4	44.8	19	22.8	22.8	10	26	23	34
14	3/8	FC-14-3	43.5	16	23.5	24.5	12	23	26	33
15	3/8	FC-15-3	43	16	23	24	12	23	26	33
16	1/2	FC-16-4	45.5	19	23.5	24.5	12	26	26	35
18	1/2	FC-18-4	47	19	24	25	15	27	30	36
20	1/2	FC-20-4	47	19	24	25	17	30	32	36
22	3/4	FC-22-6	50.2	21	25.2	25.2	18	35	35	39
25	1	FC-25-8	63	25	28.5	33.5	22	42	38	49

### (INCHES)

※管外径5φも製作しております。

1/16" : 1.6	1/8	FC-005-1	28	12	11.4	9	1.3	14	8	24
1/16" : 1.6	1/4	FC-005-2	31	15	11.4	9	1.3	17	8	27
1/8" : 3.18	1/8	FC-01-1	33	12	16	15	2.5	14	12	26
1/8" : 3.18	1/4	FC-01-2	36	15	16	15	2.5	17	12	29
1/4" : 6.35	1/8	FC-02-1	35.4	12	18.4	15.4	5	14	14	28
1/4" : 6.35	1/4	FC-02-2	36.4	15	18.4	15.4	5	17	14	29
1/4" : 6.35	3/8	FC-02-3	38.4	16	18.4	15.4	5	22	14	31
1/4" : 6.35	1/2	FC-02-4	40.4	19	18.4	15.4	5	26	14	33
5/16" : 7.94	1/4	FC-025-2	36.8	15	18.8	16.8	6	17	15.87	29
5/16" : 7.94	3/8	FC-025-3	38.8	16	18.8	16.8	6	22	15.87	31
5/16" : 7.94	1/2	FC-025-4	40.8	19	18.8	16.8	6	26	15.87	33
3/8" : 9.53	1/4	FC-03-2	38.3	15	20.3	17.8	7	17	17.46	30
3/8" : 9.53	3/8	FC-03-3	40.3	16	20.3	17.8	7	22	17.46	32
3/8" : 9.53	1/2	FC-03-4	42.3	19	20.3	17.8	7	26	17.46	34
1/2" : 12.7	1/4	FC-04-2	40.8	15	22.8	22.8	10	22	23	30
1/2" : 12.7	3/8	FC-04-3	42.8	16	22.8	22.8	10	22	23	32
1/2" : 12.7	1/2	FC-04-4	44.8	19	22.8	22.8	10	26	23	34
5/8" : 15.87	3/8	FC-05-3	43.5	16	23.5	24.5	12	23	26	33
3/4" : 19.05	1/2	FC-06-4	47	19	24	25	15	27	30	36
7/8" : 22.23	3/4	FC-07-6	50.2	21	25.2	25.2	18	35	35	39
1" : 25.4	1	FC-08-8	63	25	28	33	22	42	38	49

### (SCHEDULE)

※管外径3/8"も製作しております。

1/8B : 10.5	1/8	FC-10.5-1	38.2	12	21.2	19.2	8	17	19	29
1/8B : 10.5	1/4	FC-10.5-2	39.2	15	21.2	19.2	8	17	19	30
1/8B : 10.5	3/8	FC-10.5-3	41.2	16	21.2	19.2	8	22	19	32
1/8B : 10.5	1/2	FC-10.5-4	43.2	19	21.2	19.2	8	26	19	34
1/4B : 13.8	1/4	FC-13.8-2	43	15	23	24	12	23	26	33
1/4B : 13.8	3/8	FC-13.8-3	43	16	23	24	12	23	26	33
1/4B : 13.8	1/2	FC-13.8-4	45	19	23	24	12	26	26	35
3/8B : 17.3	3/8	FC-17.3-3	47	16	24	25	15	27	30	36
3/8B : 17.3	1/2	FC-17.3-4	47	19	24	25	15	27	30	36
1/2B : 21.7	1/2	FC-21.7-4	49.2	19	25.2	25.2	18	30	35	38
1/2B : 21.7	3/4	FC-21.7-6	50.2	21	25.2	25.2	18	35	35	39

AIC, D: FINGER TIGHT ±0.5mm (about)