



# FITTING

## BFC BULKHEAD FEMALE CONNECTOR

隔壁ハーフユニオン(メス)



(METRIC)

(Unit:mm)

TUBE O.D. T	THREADS PT or NPT	PART. No.	A	B	D	E	F	G	H	Panel Hole Size	Max. Panel Thickness
3	1/8	BFC- 3-1	48	12	15	2.5	14	12	41	8.5	10
4	1/8	BFC- 4-1	55.3	12	15.3	3.5	17	14	48	11.5	13
4	1/4	BFC- 4-2	55.3	15	15.3	3.5	17	14	48	11.5	13
6	1/8	BFC- 6-1	55.4	12	15.4	5	17	14	48	11.5	13
6	1/4	BFC- 6-2	55.4	15	15.4	5	17	14	48	11.5	13
8	1/8	BFC- 8-1	56.8	12	16.8	6	17	15.87	49	13.2	13.5
8	1/4	BFC- 8-2	56.8	15	16.8	6	17	15.87	49	13.2	13.5
10	1/4	BFC-10-2	58.7	15	18.7	8	19	19	50	16.2	14.5
10	3/8	BFC-10-3	58.7	16	18.7	8	22	19	50	16.2	14.5
12	3/8	BFC-12-3	66.8	16	22.8	10	26	23	56	19.5	16
12	1/2	BFC-12-4	66.8	21	22.8	10	26	23	56	19.5	16

※管外径5φも製作しております。

(INCHES)

1/8": 3.18	1/8	BFC- 01-1	48	12	15	2.5	14	12	41	8.5	10
1/4": 6.35	1/8	BFC- 02-1	55.4	12	15.4	5	17	14	48	11.5	13
1/4": 6.35	1/4	BFC- 02-2	55.4	15	15.4	5	17	14	48	11.5	13
5/16": 7.94	1/4	BFC-025-2	56.8	15	16.8	6	17	15.87	49	13.2	13.5
3/8": 9.53	1/4	BFC- 03-2	58.3	15	17.8	7	19	17.46	50	14.8	14.5
3/8": 9.53	3/8	BFC- 03-3	58.3	16	17.8	7	22	17.46	50	14.8	14.5
1/2": 12.7	3/8	BFC- 04-3	66.8	16	22.8	10	26	23	56	19.5	16
1/2": 12.7	1/2	BFC- 04-4	66.8	21	22.8	10	26	23	56	19.5	16


A.C.D.:FINGER TIGHT±0.5mm (about)

PFも製作できます。

※管外径3/16"も製作しております。

## FE FEMALE ELBOW

ハーフエルボ(メス)



(METRIC)

(Unit:mm)

TUBE O.D. T	THREADS PT or NPT	PART. No.	A	C	D	E	G	H
3	1/8	FE- 3-1	25	22	15	2.5	12	18
4	1/8	FE- 4-1	28.3	22	15.3	3.5	14	21
6	1/8	FE- 6-1	28.4	22	15.4	5	14	21
6	1/4	FE- 6-2	29.4	22	15.4	5	14	22
6	3/8	FE- 6-3	31.4	27	15.4	5	14	24
8	1/4	FE- 8-2	29.8	22	16.8	6	15.87	22
8	3/8	FE- 8-3	31.8	27	16.8	6	15.87	24
10	1/4	FE-10-2	31.7	22	18.7	8	19	23
10	3/8	FE-10-3	33.7	27	18.7	8	19	25
12	3/8	FE-12-3	35.8	27	22.8	10	23	25
12	1/2	FE-12-4	40.8	33	22.8	10	23	30

※管外径5φも製作しております。

(INCHES)

1/8": 3.18	1/8	FE- 01-1	25	22	15	2.5	12	18
1/4": 6.35	1/8	FE- 02-1	28.4	22	15.4	5	14	21
1/4": 6.35	1/4	FE- 02-2	29.4	22	15.4	5	14	22
1/4": 6.35	3/8	FE- 02-3	31.4	27	15.4	5	14	24
5/16": 7.94	1/4	FE-025-2	29.8	22	16.8	6	15.87	22
5/16": 7.94	3/8	FE-025-3	31.8	27	16.8	6	15.87	24
3/8": 9.53	1/4	FE- 03-2	31.3	22	17.8	7	17.46	23
3/8": 9.53	3/8	FE- 03-3	33.3	27	17.8	7	17.46	25
1/2": 12.7	3/8	FE- 04-3	35.8	27	22.8	10	23	25
1/2": 12.7	1/2	FE- 04-4	40.8	33	22.8	10	23	30

A.C.D.:FINGER TIGHT±0.5mm (about)

PFも製作できます。

※管外径3/16"も製作しております。