



MWC

MALE WELD CONNECTOR

O.D.ハーフユニオン



(METRIC)

(Unit:mm)

TUBE O.D.		PART. No.	A	B	C	D	E	F	G	H
T ₁	T ₂									
3	1/8B: 10.5	MWC- 3-1	33	11	16	15	2.5	12	12	26
4	1/8B: 10.5	MWC- 4-1	36.3	11	18.3	15.3	3.5	14	14	29
6	1/8B: 10.5	MWC- 6-1	36.4	11	18.4	15.4	5	14	14	29
6	1/4B: 13.8	MWC- 6-2	39.4	14	18.4	15.4	5	17	14	32
8	1/8B: 10.5	MWC- 8-1	36.8	11	18.8	16.8	5	14	15.87	29
8	1/4B: 13.8	MWC- 8-2	39.8	14	18.8	16.8	6	17	15.87	32
10	1/4B: 13.8	MWC-10-2	41.7	14	20.7	18.7	6	17	19	33
10	3/8B: 17.3	MWC-10-3	47.2	19	20.7	18.7	8	22	19	38.5
12	3/8B: 17.3	MWC-12-3	49.3	19	22.8	22.8	10	22	23	38.5
12	1/2B: 21.7	MWC-12-4	49.3	19	22.8	22.8	10	23	23	38.5

(INCHES)

※管外径5φも製作しております。

1/8"	3.18	1/8B: 10.5	MWC- 01-1	33	11	16	15	2.5	12	12	26
1/4"	6.35	1/8B: 10.5	MWC- 02-1	36.4	11	18.4	15.4	5	14	14	29
1/4"	6.35	1/4B: 13.8	MWC- 02-2	39.4	14	18.4	15.4	5	17	14	32
5/16"	7.94	1/8B: 10.5	MWC-025-1	36.8	11	18.8	16.8	5	14	15.87	29
5/16"	7.94	1/4B: 13.8	MWC-025-2	40.8	14	18.8	16.8	6	17	15.87	33
3/8"	9.53	1/4B: 13.8	MWC- 03-2	41.3	14	20.3	17.8	7	17	17.46	33
3/8"	9.53	3/8B: 17.3	MWC- 03-3	46.8	19	20.3	17.8	7	22	17.46	38.5
1/2"	12.7	3/8B: 17.3	MWC- 04-3	49.3	19	22.8	22.8	10	22	23	38.5
1/2"	12.7	1/2B: 21.7	MWC- 04-4	49.3	19	22.8	22.8	10	23	23	38.5


A.C.D:FINGER TIGHT±0.5mm (about)

※管外径 3/16φも製作しております。

MWE

MALE WELD ELBOW

O.D.ハーフェルボ



(METRIC)

(Unit:mm)

TUBE O.D.		PART. No.	A	B	C	D	E	G	H
T ₁	T ₂								
3	1/8B: 10.5	MWE- 3-1	25	14	24	15	2.5	12	18
4	1/8B: 10.5	MWE- 4-1	28.3	14	24	15.3	3.5	14	21
6	1/8B: 10.5	MWE- 6-1	28.4	14	24	15.4	5	14	21
6	1/4B: 13.8	MWE- 6-2	28.4	14	24	15.4	5	14	21
8	1/8B: 10.5	MWE- 8-1	28.8	14	24	16.8	6	15.87	21
8	1/4B: 13.8	MWE- 8-2	28.8	14	24	16.8	6	15.87	21
10	1/4B: 13.8	MWE-10-2	31.7	15	27	18.7	8	19	23
10	3/8B: 17.3	MWE-10-3	31.7	17	30	18.7	8	19	24
12	3/8B: 17.3	MWE-12-3	34.8	17	30	22.8	10	23	24
12	1/2B: 21.7	MWE-12-4	35.8	17	35	22.8	10	23	25

(INCHES)

※管外径5φも製作しております。

1/8"	3.18	1/8B: 10.5	MWE- 01-1	25	14	24	15	2.5	12	18
1/4"	6.35	1/8B: 10.5	MWE- 02-1	28.4	14	24	15.4	5	14	21
1/4"	6.35	1/4B: 13.8	MWE- 02-2	28.4	14	24	15.4	5	14	21
5/16"	7.94	1/8B: 10.5	MWE-025-1	28.8	14	24	16.8	6	15.87	21
5/16"	7.94	1/4B: 13.8	MWE-025-2	28.8	14	24	16.8	6	15.87	21
3/8"	9.53	1/4B: 13.8	MWE- 03-2	31.3	15	27	17.8	7	17.46	23
3/8"	9.53	3/8B: 17.3	MWE- 03-3	32.3	17	30	17.8	7	17.46	24
1/2"	12.7	3/8B: 17.3	MWE- 04-3	34.8	17	30	22.8	10	23	24
1/2"	12.7	1/2B: 21.7	MWE- 04-4	35.8	17	35	22.8	10	23	25

A.D:FINGER TIGHT±0.5mm (about)

※管外径 3/16φも製作しております。