



ADDENDUM

MA

MALE ADAPTOR

オスアダプター



(METRIC)

(Unit:mm)

T TUBE O.D.	P R or NPT	PART. No.	A	B	C	E	Ex	F
3	1/8	MA- 3-1	36	11	19	* 2	5	12
3	1/4	MA- 3-2	39	13	19	* 2	6	14
4	1/8	MA- 4-1	36	11	19	* 2.5	8	12
4	1/4	MA- 4-2	39	13	19	* 2.5	10	14
6	1/8	MA- 6-1	36	11	19	* 4	5	12
6	1/4	MA- 6-2	39	13	19	* 4	6	14
6	3/8	MA- 6-3	40	14	19	* 4	8	17
6	1/2	MA- 6-4	45.5	19	19	* 4	10	22
8	1/8	MA- 8-1	36	11	19	6	5	12
8	1/4	MA- 8-2	39	13	19	6	6	14
8	3/8	MA- 8-3	40	14	19	* 6	8	17
8	1/2	MA- 8-4	45.5	19	19	* 6	10	22
10	1/8	MA-10-1	41	11	24	8	5	12
10	1/4	MA-10-2	44	13	24	8	6	14
10	3/8	MA-10-3	45	14	24	8	8	17
10	1/2	MA-10-4	50.5	19	24	* 8	10	22
12	1/4	MA-12-2	49	13	29	10	6	14
12	3/8	MA-12-3	50	14	29	10	8	17
12	1/2	MA-12-4	55.5	19	29	10	10	22
12	3/4	MA-12-6	58.5	21	29	*10	14	27

※管外径5φも製作しております。

(INCHES)

(Unit:mm)



T TUBE O.D.	P R or NPT	PART. No.	A	B	C	E	Ex	F
1/4" : 6.35	1/8	MA- 02-1	36	11	19	* 4.35	5	12
1/4" : 6.35	1/4	MA- 02-2	39	13	19	* 4.35	6	14
1/4" : 6.35	3/8	MA- 02-3	40	14	19	* 4.35	8	17
1/4" : 6.35	1/2	MA- 02-4	45.5	19	19	* 4.35	10	22
3/8" : 9.53	1/8	MA- 03-1	41	11	24	7.5	5	12
3/8" : 9.53	1/4	MA- 03-2	44	13	24	7.5	6	14
3/8" : 9.53	3/8	MA- 03-3	45	14	24	* 7.5	8	17
3/8" : 9.53	1/2	MA- 03-4	50.5	19	24	* 7.5	10	22
1/2" : 12.7	1/4	MA- 04-2	49	13	29	10.5	6	14
1/2" : 12.7	3/8	MA- 04-3	50	14	29	10.5	8	17
1/2" : 12.7	1/2	MA- 04-4	55.5	19	29	*10.5	10	22
1/2" : 12.7	3/4	MA- 04-6	58.5	21	29	*10.5	14	27

※Ex>Eの場合、図と異なります。
※管外径3/8φも製作しております。

FA

FEMALE ADAPTOR

メスアダプター



(METRIC)

(Unit:mm)

T TUBE O.D.	P Rc or NPT	PART. No.	A	B	C	E	F
3	1/8	FA- 3-1	39	20	19	2	14
3	1/4	FA- 3-2	39	20	19	2	17
4	1/8	FA- 4-1	39	20	19	2.5	14
4	1/4	FA- 4-2	39	20	19	2.5	17
6	1/8	FA- 6-1	39	20	19	4	14
6	1/4	FA- 6-2	39	20	19	4	17
6	3/8	FA- 6-3	39	20	19	4	22
6	1/2	FA- 6-4	43	24	19	4	26
8	1/8	FA- 8-1	39	20	19	6	14
8	1/4	FA- 8-2	39	20	19	6	17
8	3/8	FA- 8-3	39	20	19	6	22
8	1/2	FA- 8-4	43	24	19	6	26
10	1/8	FA-10-1	44	20	24	8	14
10	1/4	FA-10-2	44	20	24	8	17
10	3/8	FA-10-3	44	20	24	8	22
10	1/2	FA-10-4	48	24	24	8	26
12	1/4	FA-12-2	49	20	29	10	17
12	3/8	FA-12-3	49	20	29	10	22
12	1/2	FA-12-4	53	24	29	10	26
12	3/4	FA-12-6	54	25	29	10	35

※管外径5φも製作しております。

(INCHES)

(Unit:mm)

T TUBE O.D.	P Rc or NPT	PART. No.	A	B	C	E	F
1/4" : 6.35	1/8	FA- 02-1	39	20	19	4	14
1/4" : 6.35	1/4	FA- 02-2	39	20	19	4	17
1/4" : 6.35	3/8	FA- 02-3	39	20	19	4	22
1/4" : 6.35	1/2	FA- 02-4	43	24	19	4	26
3/8" : 9.53	1/8	FA- 03-1	44	20	24	7.5	14
3/8" : 9.53	1/4	FA- 03-2	44	20	24	7.5	17
3/8" : 9.53	3/8	FA- 03-3	44	20	24	7.5	22
3/8" : 9.53	1/2	FA- 03-4	48	24	24	7.5	26
1/2" : 12.7	1/4	FA- 04-2	49	20	29	10.5	17
1/2" : 12.7	3/8	FA- 04-3	49	20	29	10.5	22
1/2" : 12.7	1/2	FA- 04-4	53	24	29	10.5	26
1/2" : 12.7	3/4	FA- 04-6	54	25	29	10.5	35

※管外径3/8φも製作しております。