

4.2mm Pitch Wire to Board LWD 1140-N Lock Wafer

Features And Specifications

Electrical


- Voltage Rating : 250VAC max
- Current Rating : 9A max
- Contact Resistance : 30m Ω max
- Insulation Resistance : 1,000M Ω min
- Dielectric Withstanding Voltage : 1000VAC for 60 seconds

Physical


- Housing : Nylon66, UL94V Grade
- Pin : 1.08mm Square Brass Pin, Tin Plated
- Operating Temperature : -40°C ~ +105°C

Reference Information

- Mates With : CHD1140-N Series
- Packing : Bag
- UL File No. : E92854
- Designed In : Millimeters



Dimensions (For Reference Only)



Ordering Information And Dimensions

CKT	MODEL NO.	A	B	CKT	MODEL NO.	A	B
2	LWD1140-02	5.4	-	14	LWD1140-14	30.6	25.2
4	LWD1140-04	9.6	4.2	16	LWD1140-16	34.8	29.4
6	LWD1140-06	13.8	8.4	18	LWD1140-18	39.0	33.6
8	LWD1140-08	18.0	12.6	20	LWD1140-20	43.2	37.8
10	LWD1140-10	22.2	16.8	22	LWD1140-22	47.4	42.0
12	LWD1140-12	26.4	21.0	24	LWD1140-24	51.6	46.2