

5.0mm Pitch Wire to Board LW 1145-N Lock Wafer

Features And Specifications

Electrical


- Voltage Rating : 250VAC max
- Current Rating : 7A max
- Contact Resistance : 30m Ω max
- Insulation Resistance : 1,000M Ω min
- Dielectric Withstanding Voltage : 1,000VAC for 60 seconds

Physical





- Housing : Nylon66, UL94V Grade
- Pin : 1.14mm Square Brass Pin, Tin Plated
- Operating Temperature : -40 $^{\circ}$ C ~ +105 $^{\circ}$ C

Reference Information

- Mates With : CH1145-N Series
- Packing : Bag
- UL File No. : E92854
- Designed In : Millimeters



Dimensions (For Reference Only)



PCB LAYOUT

Ordering Information And Dimensions

CKT	MODEL NO.	A	B	CKT	MODEL NO.	A	B
2	LW1145-02	5.00	9.40	6	LW1145-06	25.00	29.40
3	LW1145-03	10.00	14.40	7	LW1145-07	30.00	34.40
4	LW1145-04	15.00	19.40	8	LW1145-08	35.00	39.40
5	LW1145-05	20.00	24.40				